SERIES: VGS-100D | **DESCRIPTION:** INTERNAL AC-DC POWER SUPPLY

FEATURES

- wide input range (85 ~ 305 VAC)
- available with conformal coating or terminal cover options
- active Power Factor Correction (PFC)
- certified to IEC/EN/UL 62368
- designed to meet IEC/EN 61558, IEC/EN 60335, and GB4943
- output over voltage, over current, over temperature, short circuit protection
- CISPR/EN55032 Class B radiated/conducted emissions
- input over voltage category III for fixed installations




MODEL

MODEL	output voltage (Vdc)	output voltage range[1] (Vdc)	output current max (A)	output power max (W)	ripple and noise[2] max (mVp-p)	efficiency[3] typ (%)
VGS-100D-5*	5	4.75 ~ 5.5	20.0	100.0	100	86
VGS-100D-12	12	11.4 ~ 13.8	8.5	102.0	100	85
VGS-100D-15	15	14.3 ~ 16.5	6.7	100.5	100	86
VGS-100D-24	24	22.8 ~ 27.6	4.2	100.8	150	86
VGS-100D-48	48	45.6 ~ 55.2	2.1	100.8	250	87

Notes:
1. Output adjustable via built-in trimpot. The actual adjustment range may extend beyond the values listed and care should be taken to ensure the output voltage and output power do not exceed stated limits.
2. Ripple & noise are measured at 20 MHz BW with 47 µF aluminum electrolytic capacitor and 0.1 µF ceramic capacitor on the output.
3. Measured at 230 Vac
4. * Discontinued model.

PART NUMBER KEY



Please read our datasheet & drawing disclaimer here.

INPUT

parameter	conditions/description	min	typ	max	units
voltage	5 Vdc output model	85 120		264 373	Vac Vdc
	all other output models	85 120		305 430	Vac Vdc
frequency		47		63	Hz
current	at 85 Vac at 115 Vac at 230 Vac			1.7 1.3 0.7	A A A
inrush current	at 115 Vac, cold start at 230 Vac, cold start		25 45		A A
leakage current	at 240 Vac			2	mA
power factor	at 115 Vac, full load at 230 Vac, full load	0.97 0.92			

OUTPUT

parameter	conditions/description	min	typ	max	units
capacitive load	5 Vdc output 12 Vdc output 15 Vdc output 24 Vdc output 48 Vdc output			5,000 5,000 5,000 4,200 2,200	µF µF µF µF µF
initial set point accuracy	at full load 5, 12 & 15 Vdc output 24 & 48 Vdc output		 ±2 ±1		 % %
line regulation			±0.5		%
load regulation	0%~100% load 5 Vdc output model all other output models		 ±1.0 ±0.5		 % %
hold-up time	at 230 Vac	16			ms
temperature coefficient			±0.05		%/°C
remote on/off (CTRL)	turn on (0 ~ 0.8 Vdc) turn off (4 ~ 10 Vdc)				

PROTECTIONS

parameter	conditions/description	min	typ	max	units
over voltage protection	5 Vdc output model, hiccup 12 Vdc output model, hiccup 15 Vdc output model, hiccup 24 Vdc output model, hiccup 48 Vdc output model, hiccup			7.5 16.8 20.25 32.4 60.0	Vdc Vdc Vdc Vdc Vdc
over current protection	constant current, auto-recovery	105		150	%
over temperature protection[1]	over temperature protection activation over temperature protection deactivation		 50	85	°C °C
short circuit protection	constant current, continuous, auto-recovery				

Note: 1. Over temperature protection thresholds under full load conditions.

SAFETY & COMPLIANCE

parameter	conditions/description	min	typ	max	units
isolation voltage	input to ground, 1 min, <10mA input to output, 1 min, <10mA output to ground, 1 min, <5mA	2,000 4,000 500			Vac Vac Vac
safety approvals	certified to 62368: IEC, EN, UL designed to meet 60335: EN designed to meet 61558: EN designed to meet GB4943				
safety class	Class I				
conducted emissions	CISPR32/EN55032 CLASS B				
radiated emissions	CISPR32/EN55032 CLASS B				
harmonic current	IEC/EN61000-3-2				
voltage flicker	IEC/EN 61000-3-3				
ESD	IEC/EN 61000-4-2 Contact ±6KV/Air ±8KV perf. Criteria A				
radiated immunity	IEC/EN61000-4-3 3V/m perf. Criteria B				
EFT/burst	IEC/EN61000-4-4 ±2KV perf. Criteria A				
surge	IEC/EN61000-4-5 line to line ±1kV/line to ground ±2kV perf. Criteria A				
conducted immunity	IEC/EN61000-4-6 10Vr.m.s perf. Criteria A				
voltage dips and interruptions	IEC/EN61000-4-11 0%, 70% perf. Criteria B				
MTBF	as per MIL-HDBK-217F at 25°C	300,000			hours
RoHS	yes				

ENVIRONMENTAL

parameter	conditions/description	min	typ	max	units
operating temperature	see derating curve	-30		70	°C
storage temperature		-40		85	°C
operating humidity	non-condensing	20		90	%
storage humidity	non-condensing	10		95	%

MECHANICAL


parameter	conditions/description	min	typ	max	units
dimensions	179 × 99 × 30				mm
weight	5 Vdc output model all other models		530 460		g g
cooling	natural convection				
case material	metal (AL1100, SGCC)				

MECHANICAL DRAWING

units: mm [inch]
tolerance: ±1.0 [±0.039]
wire range: 22-12 AWG
connector tightening torque: M3.5, 0.8 N·m

PIN CONNECTIONS	
PIN	Function
1	+Vo
2	+Vo
3	-Vo
4	-Vo
5	⏚
6	AC(N)
7	AC(L)

Note: At least one hole position, ①~⑥, must be securely connected to Protective Earth (PE). ⏚




CN1: KANGDAO TJC3-NAWD-2P			
PIN	FUNCTION	CONNECTOR	TERMINAL
1	RC+	KANGDAO XI-25001-2Y	KANGDAO XH2.54-TE
2	RC-		


POSITION	SCREW SPEC	L (MAX)	TORQUE (MAX)
①~⑥	M4	3mm	0.9N·m

DERATING CURVE


TEMPERATURE DERATING CURVE



INPUT VOLTAGE DERATING CURVE (25°C)




ALTITUDE DERATING CURVE




EFFICIENCY CURVES

EFFICIENCY VS INPUT VOLTAGE (full load)



EFFICIENCY VS OUTPUT LOAD



REVISION HISTORY

rev.	description	date
1.0	initial release	12/14/2020
1.01	derating and efficiency curves updated	02/08/2022
1.02	UKCA mark added	06/10/2022
1.03	max screw depth updated	03/21/2023
1.04	discontinued model VGS-100D-5	01/12/2024

The revision history provided is for informational purposes only and is believed to be accurate.

CUI INC
a bel group

Headquarters
20050 SW 112th Ave.
Tualatin, OR 97062
800.275.4899

Fax 503.612.2383
cui.com
techsupport@cui.com

CUI offers a two (2) year limited warranty. Complete warranty information is listed on our website.

CUI reserves the right to make changes to the product at any time without notice. Information provided by CUI is believed to be accurate and reliable. However, no responsibility is assumed by CUI for its use, nor for any infringements of patents or other rights of third parties which may result from its use.

CUI products are not authorized or warranted for use as critical components in equipment that requires an extremely high level of reliability. A critical component is any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.