










REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
A		INITIAL RELEASE	10 JUN2022	J.Z	W.Z
A1		REVISE	26 JUL2022	J.Z	W.Z
A2		ADD PN 2385474-3	05 JUL2023	J.Z	W.Z



FOR P/N 2385474-1



FOR P/N 2385474-*

- 1. MAX.9 TERIMINAL MISSING PER REEL PERMITTED
- 2. 3 LOOSE SPLICES PER REEL PERMITTED

TE LOGO

P/N	REV.	MATERIAL	PLATING	WIRE RANGE	INSULATION-φ	INSU-CRIMP mm	WIRE-CRIMP mm	LENGTH mm	SWS/UNSEAL
2385474-1	A	CuZn30	TIN	0.35mm ²	1.2-1.4	G=2.27 H=2.19 M=1.2	E=1.78 F=1.74	A=5.6 B=2.8 C=1.8 D=0.15 L=11.15	UNSEAL
2385474-2	A	CuZn30	TIN	0.50mm ²	1.4-1.6	G=2.78 H=2.84 M=1.6	E=2.19 F=2.05	A=5.6 B=2.8 C=1.8 D=0.2 L=11.15	
2385474-3	A	CuZn30	TIN	0.13-0.17mm ²	0.95-1.2	G=1.91 H=1.92 M=1.0	E=1.56 F=1.44	A=5.3 B=2.5 C=1.8 D=0.15 L=11.15	SWS
2377023-1	A	CuZn30	TIN	0.35mm ²	1.2-1.4	G=3.16 H=3.16 M=1.9	E=1.78 F=1.74	A=6.0 B=2.5 C=2.0 D=0.45 L=11.55	
2377023-2	A	CuZn30	TIN	0.50mm ²	1.4-1.6	G=3.49 H=3.43 M=2.1	E=2.19 F=2.05	A=6.3 B=2.8 C=2 D=0.45 L=11.55	

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN	J.ZHANG	16 JUN2022
CHK	J.GU	16 JUN2022
APVD	W.ZHANG	16 JUN2022

TE Connectivity

NAME: REM 0.64 TAB TERMINAL GROUP DRAWING

APPLICATION SPEC: 114-160148

WEIGHT: -

CUSTOMER DRAWING

SCALE: 10:1

SHEET: 1 OF 1

REV: A2