






PICK-UP AREA(REF.)


N:CIRCUITS




P.W.BOARD PATTERN DIMENSION(REF.)
(MOUNT AREA)

N:CIRCUITS


METAL MASK THICKNESS : 0.1mm
OPENING AREA : TERM.(0.7X0.3)
NAIL(1.0X0.3)







ACTUATOR OPEN CONDITION

ACTUATOR CLOSED CONDITION



SECTION Y-Y





20.5	21.08	19.5	21.7	503480-4000	40
19.5	20.08	18.5	20.7	503480-3800	38
18.5	19.08	17.5	19.7	503480-3600	36
17.5	18.08	16.5	18.7	503480-3400	34
16.5	17.08	15.5	17.7	503480-3200	32
15.5	16.08	14.5	16.7	503480-3000	30
14.5	15.08	13.5	15.7	503480-2800	28
13.5	14.08	12.5	14.7	503480-2600	26
12.5	13.08	11.5	13.7	503480-2400	24
11.5	12.08	10.5	12.7	503480-2200	22
10.5	11.08	9.5	11.7	503480-2000	20
9.5	10.08	8.5	10.7	503480-1800	18
9.0	9.58	8.0	10.2	503480-1700	17
8.5	9.08	7.5	9.7	503480-1600	16
7.5	8.08	6.5	8.7	503480-1400	14
6.5	7.08	5.5	7.7	503480-1200	12
5.5	6.08	4.5	6.7	503480-1000	10
4.5	5.08	3.5	5.7	503480-0800	8
3.5	4.08	2.5	4.7	503480-0600	6
D	C	B	A	EMBOSSED PACKAGE ORDER NO.	CIRCUIT

CONNECTOR SERIES No. 503480-**09

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

DIMENSION UNITS	SCALE
mm	1:1

GENERAL TOLERANCES (UNLESS SPECIFIED)

ANGULAR TOL	±	1.0 °
4 PLACES	±	0.2
3 PLACES	±	0.2
2 PLACES	±	0.2
1 PLACE	±	0.2
0 PLACES	±	0.2

DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS

CURRENT REV DESC: REMOVED OBSOLETED PART NUMBERS AS PER PCN#513389.

EC NO: 781755
DRWN: RAVINR1 2024/03/11
CHK'D: GGA 2024/04/10
APPR: GGA 2024/04/10

INITIAL REVISION:
DRWN: THIRAYAMA 2009/12/11
APPR: KMORIKAWA 2009/12/14

THIRD ANGLE PROJECTION | DRAWING: A3-SIZE | SERIES: 503480

molex

0.5 FPC CONN. E/O
BACKFLIP H=1.0MM ASSEMBLY

PRODUCT CUSTOMER DRAWING

DOCUMENT NUMBER	DOC TYPE	DOC PART	REVISION
SD-503480-001	PSD	001	J1

MATERIAL NUMBER	CUSTOMER	SHEET NUMBER
SEE TABLE	GENERAL MARKET	1 OF 2

DOCUMENT STATUS	P1	RELEASE DATE	2024/04/10 10:13:32

FORMAT: master-tb-prod-A3
REVISION: J1
DATE: 2021/05/01

NOTES

1. PART COMPOSITION

HOUSING MATERIAL:LIQUID CRYSTAL POLYMER(LCP), GLASS FILLED, UL94V-0, NATURAL(WHITE)

TERMINAL MATERIAL:PHOSPOHR BRONZE

CONTACT AREA : SEPARATED GOLD PLATING (0.1 MICROMETER MINIMUM)
SOLDER TAIL AREA : SEPARATED GOLD PLATING
UNDERPLATE : NICKEL OVERALL (1.0 MICROMETER MINIMUM)

ACTUATOR MATERIAL : POLYAMIDE(PA), GLASS FILLED, UL94 HB, BLACK

NAIL MATERIAL:PHOSPOHR BRONZE

SOLDER TAIL AREA : TIN OVERALL(1.0 MICROMETER MINIMUM)
UNDERPLATE : NICKEL OVERALL(1.0 MICROMETER MINIMUM)

2 . PLEASE DO NOT OPERATE THE ACTUATOR BEFORE MOUNTING.

3. PLEASE OPERATE THE ACTUATOR AFTER INSERTING THE FPC INTO THE CONNECTOR.

4. ABOUT FPC
RECOMMENDED STIFFENER MATERIAL: POLYIMIDE
RECOMMENDED BASE FILM THICKNESS: 25 MICROMETER
RECOMMENDED ADHESIVE: THERMOSETTING ADHESIVE
NOTE: PLEASE PUT APPROPRIATE AMOUNT OF ADHESIVE ON ADHEREND BECAUSE THERE IS A POSSIBILITY THAT THE EXTRA ADHESIVE CAUSES THE DEFECT IN ELECTRICAL CONTINUITY.

RECOMMENDED PUNCHER DIRECTION:
FROM CONDUCTOR SIDE TO STIFFENER FILM SIDE.
RECOMMENDED CONDUCTOR SPECIFICATION:
THICKNESS OF SOFT COPPER FOIL: 35MICROMETER

△5 R0.3 MUST NOT BE OVERLAPPED TO PATTERN OF FPC.


6. COPLANARITY : 0.1 MAXIMUM

7. PLEASE RECOGNIZE A POSSIBILITY TO CHANGE THE SHAPE OF THE PART THAT DOES NOT OBSTRUCT A FUNCTION, BY CIRCUMSTANCES IN OUR PRODUCTION.

8. THIS PRODUCT IS DELIVERED WITH THE ACTUATOR IN THE OPEN POSITION.

9. THIS PRODUCT IS DUAL-CONTACT (TOP- AND BOTTOM-CONTACTS) TYPE CONNECTOR.


△10 PLEASE CONFIRM TO INSERT FPC IN ADVANCE WHEN FPC WIDTH IS OVER 0.5(N+1)+0.02.



APPLICABLE FPC RECOMMENDED DIMENSION


N:CIRCUITS

(THICKNESS : 0.3±0.05) : 30 OR LESS CIRCUITS
(THICKNESS : 0.3±0.03) : 31 OR OVER CIRCUITS



APPLICABLE FFC RECOMMENDED DIMENSION

N:CIRCUITS



STRUCTURE OF FPC

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

DIMENSION UNITS	mm
SCALE	1:1
GENERAL TOLERANCES (UNLESS SPECIFIED)	
ANGULAR TOL ±	1.0 °
4 PLACES ±	0.2
3 PLACES ±	0.2
2 PLACES ±	0.2
1 PLACE ±	0.2
0 PLACES ±	0.2
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	

CURRENT REV DESC: REMOVED OBSOLETED PART NUMBERS AS PER PCN#513389.

EC NO: 781755
DRWN: RAVINR1 2024/03/11
CHK'D: GGA 2024/04/10
APPR: GGA 2024/04/10

INITIAL REVISION:
DRWN: THIRAYAMA 2009/12/11
APPR: KMORIKAWA 2009/12/14

THIRD ANGLE PROJECTION | DRAWING: A3-SIZE | SERIES: 503480

molex

0.5 FPC CONN. E/O
BACKFLIP H=1.0MM ASSEMBLY


PRODUCT CUSTOMER DRAWING


DOCUMENT NUMBER	DOC TYPE	DOC PART	REVISION
SD-503480-001	PSD	001	J1


MATERIAL NUMBER	CUSTOMER	SHEET NUMBER
SEE TABLE	GENERAL MARKET	2 OF 2

DOCUMENT STATUS	P1	RELEASE DATE	2024/04/10 10:13:32

FORMAT: master-lb-prod-A3
REVISION: J1
DATE: 2021/05/01








NOTES

1. IN THE PACKAGE, PART NO.503480-**09 DETAILED DIMENSIONS.
   REFER TO SD-503480-001

2. NUMBER OF CONNECTORS : 3000PCS/REEL

3. LEAD TAPE LENGTH



4. MATERIAL
   CARRIER TAPE : PET
   TOP TAPE : PET,OTHER
   REEL : PS (RECYCLE MATERIAL CONTAINED)

5. COVER TAPE PEEL FORCE IS DEFINED BY IEC60286-3.

F	E	D	C	B	A	TAPE WIDTH	ORDER NO.	CIRCUIT
380	20.2	40.4	44	-	-	44	503480-4000	E1 40
							503480-3800	E1 38
							503480-3600	E1 36
330	14.2	28.4	32			32	503480-3400	E1 34
							503480-3200	32
380							503480-3000	E1 30
	-	-	-	11.5	24	24	503480-2800	E1 28
							503480-2600	26
							503480-2400	24
							503480-2200	22
							503480-2000	20
							503480-1800	18
330							503480-1700	17
							503480-1600	16
							503480-1400	14
	-	-	-	7.5	16	16	503480-1200	12
							503480-1000	10
							503480-0800	8
							503480-0600	6

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

DIMENSION UNITS	SCALE
mm	NTS

GENERAL TOLERANCES (UNLESS SPECIFIED)

ANGULAR TOL ±	3.0 °
4 PLACES	±
3 PLACES	±
2 PLACES	±
1 PLACE	±
0 PLACES	±

DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS

10 UNDER : ±0.20
10 OVER 30 UNDER : ±0.25
30 OVER : ±0.30

CURRENT REV DESC: REMOVED OBSOLETED PART NUMBERS AS PER PCN#513389.

EC NO: 781755
DRWN: RAVINR1 2024/03/11
CHK'D: GGA 2024/04/10
APPR: GGA 2024/04/10

INITIAL REVISION:
DRWN: THIRAYAMA 2009/12/11
APPR: KMORIKAWA 2009/12/14

THIRD ANGLE PROJECTION | DRAWING: A3-SIZE | SERIES: 503480

molex

0.5 FPC CONN. E/O
EMBOSSED TAPE PACKAGE

PRODUCT CUSTOMER DRAWING

DOCUMENT NUMBER	DOC TYPE	DOC PART	REVISION
SD-503480-002	PSD	001	E3

MATERIAL NUMBER	CUSTOMER	SHEET NUMBER
SEE TABLE	GENERAL MARKET	1 OF 1

DOCUMENT STATUS	P1	RELEASE DATE	2024/04/10 10:13:33

FORMAT: master-tb-prod-A3
REVISION: J1
DATE: 2021/05/01