

STRAIGHT PCB RECEPTACLE

-


R128.425.300


Series : **BMA**





	mm	
	Maxi	mini
A	-	1.3
B	-	1.7
C	5.13	5.03





All dimensions are in mm.

COMPONENTS	MATERIALS	PLATING (µm)
BODY	**STAINLESS STEEL**	**GOLD 0.5 OVER NICKEL 2**
CENTER CONTACT	**BERYLLIUM COPPER**	**GOLD 1.3 OVER NICKEL 2**
OUTER CONTACT	-	-
INSULATOR	**PTFE**	
GASKET	**SILICONE RUBBER**	
OTHERS PARTS	-	-
-	-	-
-	-	-

Issue : 1149 B

In the effort to improve our products, we reserve the right to make changes judged to be necessary.

RADIALL

STRAIGHT PCB RECEPTACLE

-

R128.425.300

Series : **BMA**

PACKAGING

Standard	Unit	Other
100	**'W' option**	**Contact us**

SPECIFICATION

ELECTRICAL CHARACTERISTICS

Impedance	**50**	Ω
Frequency	**0-22**	GHz
VSWR	**- + 0,0000**	x F(GHz) Maxi
Insertion loss	**-**	√F(GHz) dB Maxi
RF leakage	**- (-**	- F(GHz)) dB Maxi
Voltage rating	**350**	Veff Maxi
Dielectric withstanding voltage	**1000**	Veff mini
Insulation resistance	**5000**	MΩ mini

ENVIRONMENTAL

Operating temperature	**-65/+125**	° C
Hermetic seal	**-**	Atm.cm3/s
Panel leakage	**-**	

OTHER CHARACTERISTICS

Assembly instruction

Others :
-

MECHANICAL CHARACTERISTICS

Center contact retention		
Axial force – Mating end	**27**	N mini
Axial force – Opposite end	**27**	N mini
Torque	**NA**	N.cm mini
Recommended torque		
Mating	**-**	N.cm
Panel nut	**-**	N.cm
Mating life	**1000**	Cycles mini
Weight	**0,2100**	g

In the effort to improve our products, we reserve the right to make changes judged to be necessary.

RADIALL