



SIGN	DATE	DESCRIPTION	APPROVER
1	09/15`11	The color is changed from RAL7035/D to RAL7004/P	Runner
2	09/15`11	The dimension is changed from 2.1 to 2.2	Runner
3	09/15`11	The Material is changed	Runner
4	09/15`11	The tolerance is changed	Runner
5	09/25`13	change the dimension from 18.6&2.6 to 19.2&3.2	Da cheng
6	09/25`13	change the electrical specification	Da cheng


THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!














P.C.B Layout
6 Top view

Material:

- Item Ⓐ Terminal body: Thermoplastic (UL94V-0)
- Item Ⓑ Terminal side body: Thermoplastic (UL94V-0)
- Item Ⓒ Terminal cover: Thermoplastic (UL94V-0)
- 5 Item Ⓓ Contact pin : Copper, Tin Plated.
- Item Ⓔ Spring clamp : Stainless steel

6 Electrical:

Voltage rating:	300 V
Current rating(Sol):	30 A
Current rating(Str):	35 A
Solid wire(AWG):	10-24
Stranded wire(AWG):	8-24
Wire strip length:	15-16 mm
Withstanding Voltage:	1.6KV
Operating temperature:	-40°C to +120°C
Soldering temperature:	260°C±5°C/5 Sec
Safety Approval:	cULus
Critical dimension:	C

NK xx A 0 x 0 xxxx G

- xx: End Stackable
  - 01: 1 POLES
  - 02: 2 POLES
  - :
  - 16: 16 POLES
- A: RoHS compliant (lead<4%)
- x: 6 Body Color
  - 0 Black (RAL9005)
  - 2 Red (RAL3001/D)
  - 3 Orange(RAL2011/P)
  - 4 Yellow(RAL1018/A)
  - 5 Green(RAL6018/T)
  - 6 Blue (RAL5015/A)
  - 1 8 Grey(RAL7004/P)
  - 9 White(RAL1102)
  - C Multiple colors
- xxxx: In copper Alloy
  - 0000: "@" Logo (Standard)
  - 000A: "ANYTEK" Mark
  - Any special item by customer requst. please contact sales department.
- G: RoHS compliant (lead<4%)

N=NUMBER OF POLES 4

DIM		TOL 1P--6P	TOL 7P--12P	TOL 13P--16P
Dim P	(N-1)×7.5	±0.15	±0.25	±0.35
Dim L	N×7.5+1.8	±0.15	±0.25	±0.35

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	NK 7.5mm Series Vertical (Double tail A type)(平行脚)				
PART NO.	NKxxA0x0xxxxG			DWG NO.	8NK0001
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.	
		Da cheng 2013.09.25	Da cheng 2013.09.25	UNIT: mm SCALE: NONE SHEET: 01/01 REV.: C	

Tolerance	
X.	±0.50
X.X	±0.30
X.XX	±0.10
X°	±1°