




PANEL CUT-OUT

| PANEL CUT-OUT |             |             |
|---------------|-------------|-------------|
| Z             | Y           | X           |
| 1.25~2.00     | 21.20~21.40 | 28.90~29.20 |
| 2.00~3.00     | 21.20~21.40 | 29.30~29.50 |

#### NOTES:

##### 1. Rating:

CQC CE 16A 250V AC

20A 125V AC

##### 2. Circuit Diagram: 4P ON-OFF-ON

##### 3. Terminal Strength: $\geq 80N$

##### 4. Electrical life: $\geq 10000$ cycles

5. Withstand Voltage: Withstand Voltage: 1500VAC 1min  
Terminals to Button: 3000VAC 1min  
Leakage Current: 1mA



##### 6. Current resistance: $\leq 50m\Omega$ (initial)

##### 7. Insulation resistance: $\geq 100M\Omega$

##### 8. Body Material: NYLON 66 94V-0<sup>2</sup>

##### 9. Operating Force: 4N-8N

#### SWITCHING CIRCUIT



|      |      |                         |       |                            |       |                 |              |                    |                                                                                       |                     |                      |              |      |
|------|------|-------------------------|-------|----------------------------|-------|-----------------|--------------|--------------------|---------------------------------------------------------------------------------------|---------------------|----------------------|--------------|------|
| A4   |      |                         |       | 普通公差：<br>COMMON TOLERANCE： |       |                 |              |                    |                                                                                       |                     |                      |              |      |
| A3   |      |                         |       |                            |       |                 |              |                    |                                                                                       |                     |                      |              |      |
| A2   |      |                         |       | UP TO 5                    | ±0.20 | 单 位<br>UNIT     | mm           | 投 影<br>PROJECTED   |  | 品 名<br>PRODUCT NAME | 跷板开关                 | 比 例<br>SCALE | Free |
| A1   |      |                         |       | ABOVE 5 TO 30              | ±0.30 | 绘 图<br>DRAWN BY | 吴 瑜          | 核 对<br>CHECKED BY  |                                                                                       | 型 号<br>MODEL NO.    | KCD4-201N-6P-R       |              |      |
| REV. | DATE | REVISION<br>DESCRIPTION | ISSUE | ABOVE 30                   | ±0.50 | 日 期<br>DATE     | 2022. 11. 10 | 核 准<br>APPROVAL BY |                                                                                       | 图 号<br>DWG NO.      | LANZ/CRS-KCD4201N6PR |              |      |
|      |      |                         |       | ANGULAR                    | ±5°   |                 |              |                    |                                                                                       |                     |                      |              |      |