

61134-3 ✓ ACTIVE

FASTON | FASTON 110


TE Internal #: 61134-3

Tab, Mating Tab Width 2.79 mm [.11 in], PCB Hole Diameter 4.1 mm [.161 in], Through Hole - Solder, Tin Plating, Brass, Bag, FASTON 110, PCB Terminals

[View on TE.com >](#)



Terminals & Splices > PCB Terminals



PCB Terminal Type: **Tab**

PCB Thickness (Recommended): .81 – 2.36 mm [.032 – .093 in]

Mating Tab Width: 2.79 mm [.11 in]

Mating Tab Thickness: .51 mm [.02 in]

PCB Hole Diameter: 4.1 mm [.161 in]

## Features

### Contact Features

PCB Contact Termination Area Plating Material Thickness	3.81 µm[150 µin]
Contact Underplating Material Thickness	2.54 µm[100 µin]
Contact Mating Area Plating Material Thickness	3.81 µm[150 µin]
PCB Terminal Type	Tab
Mating Tab Width	2.79 mm[.11 in]
Mating Tab Thickness	.51 mm[.02 in]
Terminal Plating Material	Tin
Contact Underplating Material	Brass
Terminal Size	2.8
Terminal Orientation	Straight

### Termination Features

Termination Method to PCB	Through Hole - Solder
Product Terminates To	Printed Circuit Board

### Mechanical Attachment



Wire Insulation Support	With
-------------------------	------

### Dimensions

PCB Thickness (Recommended)	.81 – 2.36 mm [.032 – .093 in]
PCB Hole Diameter	4.1 mm [.161 in]

### Usage Conditions

Insulation Option	Uninsulated
Operating Temperature Range	-30 – 110 °C [-22 – 230 °F]

### Industry Standards

Compatible With Agency/Standards Products	CSA, UL
---	---------

### Packaging Features

Packaging Quantity	1000
Packaging Method	Bag

## Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Pin-in-Paste capable to 260°C

#### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts

<p>TE Part # 63067-1 250 FASTON TAB TPBR</p>	<p>TE Part # 735427-2 110 FASTON TAB TPBR</p>	<p>TE Part # 1217169-1 250 FASTON,PCB TAB,TCBR</p>	<p>TE Part # 62409-1 250 FASTON TAB TPBR</p>
<p>TE Part # 1217057-1 187 FASTON,PCB TAB,TPBR</p>	<p>TE Part # 63982-1 187 FASTON TAB TPBR</p>	<p>TE Part # 1217056-1 250 FASTON,PCB TAB,TPBR</p>	<p>TE Part # 62437-1 110 FASTON TAB TPBR</p>
<p>TE Part # 63900-1 250 FASTON TAB TPBR</p>	<p>TE Part # 60284-2 205 FASTON TAB TPBR</p>	<p>TE Part # 725996-2 110 FASTON TAB TPBR</p>	<p>TE Part # 1-1217121-1 110 FASTON,PCB TAB,TPBR</p>

## Also in the Series | FASTON 110

<p>Crimp Terminal Housings(13)</p>	<p>Insertion &amp; Extraction Tools(1)</p>	<p>PCB Terminals(22)</p>	<p>Quick Disconnects(168)</p>
------------------------------------	--	--------------------------	-------------------------------

## Customers Also Bought




TE Part #D98213-000  
T1K-165051-25-9



TE Part #5-2176070-5  
3521 1K8 1% 2W



TE Part #2-1393143-4  
27E212=SOCKET,R10,10,PC,PHEN



TE Part #170430-1  
EI PIN LP 170377-1 LP



TE Part #8-34105-1  
SOLIS R 22-16 COMM 22-18 MIL 6



TE Part #3-2176327-4  
CRGP 0805 5K6 1%



TE Part #7-1879354-7  
RR03 5% 470R AMMO



TE Part #177899-2  
POWER DBL LOCK PLUG 3P RED



TE Part #1-929278-2  
MOS STIFT M.A-PIN



TE Part #5-2176453-9  
CPF 0201 23K2 0.1% 25ppm 1K RL

## Documents

### Product Drawings

#### 110 FASTON TAB TPBR

English

### CAD Files

#### 3D PDF

3D

#### Customer View Model

[ENG\\_CVM\\_CVM\\_61134-3\\_AE\\_c-61134-3-ae.2d\\_dxf.zip](#)

English

#### Customer View Model

[ENG\\_CVM\\_CVM\\_61134-3\\_AE\\_c-61134-3-ae.3d\\_igs.zip](#)

English

#### Customer View Model

[ENG\\_CVM\\_CVM\\_61134-3\\_AE\\_c-61134-3-ae.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

### Datasheets & Catalog Pages



### [FASTON PCB Tabs and Receptacles](#)

English

### [PRINTED CIRCUIT BOARD TERMINALS AND DISCONNECTS](#)

English

---

### [Product Specifications](#)

#### [Application Specification](#)

English

---

### [Agency Approvals](#)

#### [CSA Certificate](#)

English

#### [CSA Certificate](#)

English