11MHZ CMOS Rail-to-Rail IO Opamps

Features

- Single-Supply Operation from +2.1V ~ +5.5V
- Rail-to-Rail Input / Output
- Gain-Bandwidth Product: 11MHz (Typ.)
- Low Input Bias Current: 1pA (Typ.)
- Low Offset Voltage: 3.5mV (Max.)
- High Slew Rate: 9V/μs
- Settling Time to 0.1% with 2V Step: 0.3μs
- Low Noise : 8nV/ Hz @10kHz
- Quiescent Current: 1.1mA per Amplifier (Typ.)
- Operating Temperature: -40°C ~ +85°C
- Small Package:
  HGV6021 Available in SOT23-5,MSOP-8 and SC70-5 Packages
  HGV6022 Available in SOP-8 and MSOP-8 Packages
  HGV6024 Available in SOP-14 and TSSOP-14 Packages



Package/Ordering Information

DEVICE	Package Type	MARKING	Packing	Packing Qty
HGV6021M5/TR	SOT-23-5	6021	REEL	3000pcs/reel
HGV6021M7/TR	SC70-5(SOT-353)	6021	REEL	3000pcs/reel
HGV6021M/TR	SOP-8	V6021	REEL	2500pcs/reel
HGV6021MM/TR	MSOP-8	V6021	REEL	3000pcs/reel
HGV6022M/TR	SOP-8	V6022	REEL	2500pcs/reel
HGV6022MM/TR	MSOP-8	V6022	REEL	3000pcs/reel
HGV6024M/TR	SOP-14	HGV6024	REEL	2500pcs/reel
HGV6024MT/TR	TSSOP-14	V6024	REEL	2500pcs/reel

General Description

The HGV602X have a high gain-bandwidth product of 11MHz, a slew rate of 9Vμ/s, and a quiescent current of 1.1mA peramplifier at 5V. The HGV602X are designed to provideoptimal performance in low voltage and low noise systems. They provide rail-to-rail output swing into heavy loads. The input common mode voltage range includes ground, and the maximum input offset voltage is 3.5mV for HGV602X. They are specified over the extended industrial temperature range (-40 ℃ to +85 ℃). The operating range is from 2.1V to 5.5V. The HGV6021 sin gle is available in Green SC70-5, SOT-23-5,MSOP-8 and SOP-8 packages. The HGV6022 dual is available in Green SOP-8 and MSOP-8 pa ckages. The HGV6024 Quad is available in Green SOP-14and TSSOP-14 packages.

Applications

- Sensors
- Active Filters
- Cellular and Cordless Phones
- Laptops and PDAs
- Audio
- Handheld Test Equipment
- Battery-Powered Instrumentation
- A/D Converters

Pin Configuration




Figure 1. Pin Assignment Diagram

Absolute Maximum Ratings

Condition	Min	Max
Power Supply Voltage (VDD to Vss)	-0.5V	+7.5V
Analog Input Voltage (IN+ or IN-)	Vss-0.5V	VDD+0.5V
PDB Input Voltage	Vss-0.5V	+7V
Operating Temperature Range	-40°C	+85 °C
Junction Temperature	+160°C	
Storage Temperature Range	-55°C	+150°C
Lead Temperature (soldering, 10sec)	+260°C	
Package Thermal Resistance (TA=+25℃)		
SOP-8, θJA	125°C/W	
MSOP-8, θJA	216°C/W	
SOT-23-5, θJA	190°C/W	
SOT23-6, θJA	190°C/W	
SC70-5, θJA	333°C/W	
ESD Susceptibility		
HBM	8KV	
MM	400V	

Note:

Stress greater than those listed under Absolute Maximum Ratings may cause permanent damage to the device. This is astress rating only and functional operation of the device at these or any other conditions outside those indicated in the operationalsections of this specification are not implied. Exposure to absolute maximum rating conditions for extended periods may affectreliability.

Electrical Characteristics

(At Vs=5V, TA = +25℃, VCM = VS/2, RL = 600Ω, unless otherwise noted.)

PARAMETER	CONDITIONS	HGV6021/2/4					
		TYP	MIN/MAX OVER TEMPERATURE				
		+25℃	+25℃	0℃ to 70℃	-40℃ to 85℃	UNITS	MIN / MAX
INPUT CHARACTERISTICS							
Input Offset Voltage (VOS)		0.8	3.5	3.9	4.3	mV	MAX
Input Bias Current (IB)		1				pA	TYP
Input Offset Current (IOS)		1				pA	TYP
Input Common Mode Voltage Range (VCM)	VS = 5.5V	-0.1 to +5.6				V	TYP
Common Mode Rejection Ratio (CMRR)	VS = 5.5V, VCM = -0.1V to 4V	82	65	64	64	dB	MIN
	VS = 5.5V, VCM = -0.1V to 5.6V	75				dB	MIN
Open-Loop Voltage Gain (AOL)	RL = 600Ω,VO = 0.15V to 4.85V	90	80	76	75	dB	MIN
	RL = 10kΩ,VO = 0.05V to 4.95V	108				dB	MIN
Input Offset Voltage Drift (ΔVOS/T)		2.4				μV/°C	TYP
OUTPUT CHARACTERISTICS							
Output Voltage Swing from Rail	RL = 600Ω	0.1				V	TYP
	RL = 10kΩ	0.015				V	TYP
Output Current (IOUT)		70	55	45	42	mA	MIN
Closed-Loop Output Impedance	f = 100kHz, G = 1	7.5				Ω	TYP
POWER-DOWN DISABLE							
Turn-On Time		1.1				μs	TYP
Turn-Off Time		0.3				μs	TYP
DISABLE Voltage-Off			0.8			μsV	MAX
DISABLE Voltage-On			2			V	MAX
POWER SUPPLY							
Operating Voltage Range			2.1	2.1	2.1	V	MIN
			5.5	5.5	5.5	V	MAX
Power Supply Rejection Ratio (PSRR)	VS = +2.5V to +5.5V VCM =(-VS) + 0.5	91	74	72	72	dB	MIN
Quiescent Current/Amplifier (IQ)	V IOUT = 0	1.1	1.5	1.65	1.7	mA	MAX

Electrical Characteristics


(At Vs=5V, TA = +25℃, VCM = VS/2, RL = 600Ω, unless otherwise noted.)

PARAMETER	CONDITIONS	HGV6021/2/4					
		TYP	MIN/MAX OVER TEMPERATURE				
		+25℃	+25℃	0℃to 70℃	-40℃ to 85℃	UNITS	MIN / MAX
DYNAMIC PERFORMANCE							
Gain-Bandwidth Product (GBP)	R_L = 10kΩ, C_L = 100pF	11				MHz	TYP
Phase Margin (φO)	R_L = 10kΩ, C_L = 100pF	51				Degrees	TYP
Full Power Bandwidth (BWP)	＜1% distortion, R_L = 600Ω	400				kHz	TYP
Slew Rate (SR)	G = +1, 2V Step, R_L = 10kΩ	9				V/μs	TYP
Settling Time to 0.1% (t_S)	G = +1, 2V Step, R_L = 600Ω	0.3				μs	TYP
Overload Recovery Time	V_{IN} ·Gain = VS, R_L = 600Ω	1.5				μs	TYP
NOISE PERFORMANCE							
Voltage Noise Density (e_n)	f = 1kHz	11.5				$nV/\sqrt{Hz}$	TYP
	f = 10kHz	8				$nV/\sqrt{Hz}$	TYP


Typical Performance characteristics

(At Vs=5V, TA = +25℃, VCM = VS/2, RL = 600Ω, unless otherwise noted.)


Small-Signal Step Response




Small-Signal Step Response




Large-Signal Step Response




Large-Signal Step Response



Positive Overload Recovery




Negative Overload Recovery




Typical Performance characteristics

(At Vs=5V, TA = +25℃, VCM = VS/2, RL = 600Ω, unless otherwise noted.)


Output Voltage Swing vs.Output Current




Supply Current vs. Temperature




Input Voltage Noise Spectral Density vs. Frequency




Open Loop Gain, Phase Shift vs. Frequency



CMRR vs. Frequency



PSRR vs. Frequency



Application Note

Size

HGV602X series op amps are unity-gain stable and sutai ble for a wide range of general-purpose applications. The small footprints of the HGv602X series packages save spaceon printed circuit boards and enable the design of smaller electronic products.

Power Supply Bypassing and Board Layout

HGV602X series operates from a single 2.1V to 5.5V supply or dual ±1.05V to ±2.75V supplies. For best performance, a 0.1μF ceramic capacitor should be placed close to the VDD pin in single supply operation. For dual supply operation, both VDD and VSS supplies should be bypassed to ground with separate 0.1μF ceramic capacitors.

Low Supply Current

The low supply current (typical 1.1mA per channel) of HGV602X series will help to maximize battery lif.eThey are ideal for battery powered systems

Operating Voltage

HGV602X series operate under wide input supply voltage (2.1V to 5.5V). In addition, all temperature speci fications apply from-40 °C to +85 °C. Most behavior remains unchanged throughout the full operating voltage range. These guarantees ensure operation throughout the single Li-Ion battery lifetime

Rail-to-Rail Input

The input common-mode range of HGV602X series extends 100mV beyond the supply rails (VSS-0.1V to VDD+0.1V). This is achieved by using complementary input stage. For normal operation, inputs should be limited to this range.

Rail-to-Rail Output

Rail-to-Rail output swing provides maximum possible dynamic range at the output. This is particularly important when operating in low supply voltages. The output voltage of HGV602X series can typically swing to less than2mV from supply rail in light resistive loads (>100kΩ), and 15mV of supply rail in moderate resistive loads (10kΩ).

Capacitive Load Tolerance

The HGV602X family is optimized for bandwidth and speed, not for driving capacitive loads. Output capacitance will create a pole in the amplifier’s feedback path, leading to excessive peaking and potential oscillation. If dealing with load capacitance is a requirement of the application, the two strategies to consider are (1) using a small resistor in series with the amplifier’s output and the load capacitance and (2) reducing the bandwidth of the amplifier’s feedback loop by increasing the overall noise gain. Figure 2. shows a unity gain follower using the series resistor strategy. The resistor isolates the output from the capacitanceand, more importantly, creates a zero in the feedback path that compensates for the pole created by the output capacitance.




Figure 2. Indirectly Driving a Capacitive Load Using Isolation Resistor

The bigger the RISO resistor value, the more stable VOUT will be. However, if there is a resistive load RL in parallel with the capacitive load, a voltage divider (proportional to RISO/RL) is formed, this will result in a gain error.

The circuit in Figure 3 is an improvement to the one in Figure 2. RF provides the DC accuracy by feed-forward the VIN to RL. CFand RISO serve to counteract the loss of phase margin by feeding the high frequency component of the output signal back to the amplifier's inverting input, thereby preserving the phase margin in the overall feedback loop. Capacitive drive can be increased by increasing the value of CF. This in turn will slow down the pulse response.




Figure 3. Indirectly Driving a Capacitive Load with DC Accuracy

Typical Application Circuits

Differential amplifier

The differential amplifier allows the subtraction of two input voltages or cancellation of a signal common the two inputs. It is useful as a computational amplifier in making a differential to single-end conversion or in rejecting a common mode signal. Figure 4. shown the differential amplifier using HGV602X.




Figure 4. Differential Amplifier


$$V_{OUT}=\left(\frac{R_1+R_2}{R_3+R_4}\right)\frac{R_4}{R_1}V_{IN}-\frac{R_2}{R_1}V_{IP}+\left(\frac{R_1+R_2}{R_3+R_4}\right)\frac{R_3}{R_1}V_{REF}$$

If the resistor ratios are equal (i.e. $R_1=R_3$ and $R_2=R_4$), then

$$V_{OUT}=\frac{R_2}{R_1}(V_{IP}-V_{IN})+V_{REF}$$

Low Pass Active Filter

The low pass active filter is shown in Figure 5. The DC gain is defined by –R2/R1. The filter has a -20dB/decade roll-off after its corner frequency fC=1/(2πR3C1).



Instrumentation Amplifier

The triple HGV602X can be used to build a three-op-ma p instrumentation amplifier as shown in Figure 6. The amplifier in Figure 6 is a high input impedance differential amplifier with gain of R2/R1. The two differential voltage followers assure the high input impedance of the amplifier.





Figure 6. Instrument Amplifier

Physical Dimensions


SOP-8



1 Package top mark may be in lower left corner or unmark

Dimensions In Millimeters(SOP-8)									
Symbol:	A	A1	B	C	C1	D	Q	a	b
Min:	1.35	0.05	4.90	5.80	3.80	0.40	0°	0.35	1.27 BSC
Max:	1.55	0.20	5.10	6.20	4.00	0.80	8°	0.45	


MSOP-8



Dimensions In Millimeters(MSOP-8)									
Symbol:	A	A1	B	C	C1	D	Q	a	b
Min:	0.80	0.05	2.90	4.75	2.90	0.35	0°	0.25	0.65 BSC
Max:	0.90	0.20	3.10	5.05	3.10	0.75	8°	0.35	


Physical Dimensions

SOP-14



Dimensions In Millimeters(SOP-14)									
Symbol:	**A**	**A1**	**B**	**C**	**C1**	**D**	**Q**	**a**	**b**
Min:	1.35	0.05	8.55	5.80	3.80	0.40	0°	0.35	1.27 BSC
Max:	1.55	0.20	8.75	6.20	4.00	0.80	8°	0.45	


TSSOP-14



Dimensions In Millimeters(TSSOP-14)									
Symbol:	A	A1	B	C	C1	D	Q	a	b
Min:	0.85	0.05	4.90	6.20	4.30	0.40	0°	0.20	0.65 BSC
Max:	0.95	0.20	5.10	6.60	4.50	0.80	8°	0.25	


Physical Dimensions

SOT-23-5



Dimensions In Millimeters(SOT-23-5)										
Symbol:	A	A1	B	C	C1	D	Q	a	b	e
Min:	1.00	0.00	2.82	2.65	1.50	0.30	0°	0.30	0.95 BSC	1.90 BSC
Max:	1.15	0.15	3.02	2.95	1.70	0.60	8°	0.50		

SC70-5



Dimensions In Millimeters(SC70-5)										
Symbol:	A	A1	B	C	C1	D	Q	a	b	e
Min:	0.90	0.00	2.00	2.15	1.15	0.26	0°	0.15	0.65 BSC	1.30 BSC
Max:	1.00	0.15	2.20	2.45	1.35	0.46	8°	0.35		

Revision History

REVISION NUMBER	DATE	REVISION	PAGE
V1.0	2015-3	New	1-15
V1.1	2018-10	Update encapsulation type、Update SC70-5 Physical Dimensions	1、13
V1.2	2024-10	Update SOT-23-5 Physical dimension、Update Lead Temperature	13、3
V1.3	2025-12	Update important statements、Update SOP-8 and SOP-14 Dimension drawing	11、12

IMPORTANT STATEMENT:

Huaguan Semiconductor reserves the right to change products and services offered without prior notice. Customers should obtain the latest relevant information before placing orders and verify that such information is current and complete. Huaguan Semiconductor assumes no responsibility or liability for altered documents.

Customers are responsible for complying with safety standards and implementing safety measures when using Huaguan Semiconductor products in system design and end-product manufacturing. You assume full responsibility for: selecting the appropriate Huaguan Semiconductor products for your application; designing, validating, and testing your application; and ensuring that your application complies with applicable standards and all other safety, security, or other requirements. This is to prevent potential risks that may lead to personal injury or property damage.

Huaguan Semiconductor products are not approved for use in life support, military, aerospace, or other high-risk applications. Huaguan products are neither intended nor warranted for use in such systems or equipment. Any failure or malfunction may lead to personal injury or severe property damage. Such applications are deemed "Unsafe Use." Unsafe Use includes, but is not limited to: surgical and medical equipment, nuclear energy control equipment, aircraft or spacecraft instruments, control or operation of vehicle power, braking, or safety systems, traffic signal instruments, all types of safety devices, and any other applications intended to support or sustain life. Huaguan Semiconductor shall not be liable for consequences resulting from Unsafe Use in these fields. Users must independently evaluate and assume all risks. Any issues, liabilities, or losses arising from the use of products beyond their approved applications shall be solely borne by the user. Users may not claim any compensation from Huaguan Semiconductor based on these terms. If any third party claims against Huaguan Semiconductor due to such Unsafe Use, the user shall compensate Huaguan Semiconductor for all resulting damages and liabilities.

Huaguan Semiconductor provides technical and reliability data (including datasheets), design resources (including reference designs), application or other design advice, web tools, safety information, and other resources for its semiconductor products. However, no guarantee is made that these resources are free from defects, and no express or implied warranties are provided. The use of testing and other quality control techniques is limited to Huaguan Semiconductor's quality assurance scope. Not all parameters of each device are tested.

Huaguan Semiconductor's documentation authorizes you to use these resources only for developing applications related to the products described herein. You are not granted rights to any other intellectual property of Huaguan Semiconductor or any third party. Any other reproduction or display of these resources is strictly prohibited. You shall fully indemnify Huaguan Semiconductor and its agents against any claims, damages, costs, losses, and liabilities arising from your use of these resources. Huaguan Semiconductor shall not be held responsible.