

产品参数/Product parameters



额定电流 (Rated current):	3A AC/DC
盐雾实验 (Life Test):	24 hours
接触电阻 (Contact Resistance):	20mΩ
绝缘电阻 (Insulation Resistance):	1000MΩ min.
耐电压 (Withstand voltage):	AC 1000V
工作温度 (Operating Temperature):	-40° C to 105°
防火等级 (Fire rating):	Polyester (UL94V-0)
触点电镀 (Dielectric Strength):	Gold Flash
耐高温范围/时长 (High temperature resistance range/duration):	260° C for 5 seconds
包装方式 (Packaging method):	袋装

**产品名称**  
Product name

- ▶ 2.54PH H2.5 2\*Pin 180
- ▶ 度 双排插件 PC3.0 PA6.0 PB2.5 L11.5

**产品应用场景**  
Product application scenario

- ▶ 电子通讯/数码产品/家用电器
- ▶ 外围设备/汽车/医疗设备等.
- ▶ Electronic communication/digital products/household appliance peripherals/AuTomotive/medical equipment, etc

材质/MATERIALS:

No.	名称/NAME	材料/MATERIAL	表面处理/颜色 Surfacetreatment/color
①	端子/Terminal	Brass/C2680	镀金 gold-plating
②	塑胶/plastic cement	PBT/PA6T	黑色 Black

排针系列™  
Needle arrangement series™

产品PIN位示意图/Schematic diagram of product PIN

No. of	DIM. A	DIM. B	No. of	DIM. A	DIM. B	No. of	DIM. A	DIM. B	No. of	DIM. A	DIM. B
2*1P	0.00	2.54	2*11P	25.40	27.94	2*21P	50.80	53.34	2*31P	76.20	78.74
2*2P	2.54	5.08	2*12P	27.94	30.48	2*22P	53.34	55.88	2*32P	78.74	81.28
2*3P	5.08	7.62	2*13P	30.48	33.02	2*23P	55.88	58.42	2*33P	81.28	83.82
2*4P	7.62	10.16	2*14P	33.02	35.56	2*24P	58.42	60.96	2*34P	83.82	86.36
2*5P	10.16	12.70	2*15P	35.56	38.10	2*25P	60.96	63.50	2*35P	86.36	88.90
2*6P	12.70	15.24	2*16P	38.10	40.64	2*26P	63.50	66.04	2*36P	88.90	91.44
2*7P	15.24	17.78	2*17P	40.64	43.18	2*27P	66.04	68.58	2*37P	91.44	93.98
2*8P	17.78	20.32	2*18P	43.18	45.72	2*28P	68.58	71.12	2*38P	93.98	96.52
2*9P	20.32	22.86	2*19P	45.72	48.26	2*29P	71.12	73.66	2*39P	96.52	99.06
2*10P	22.86	25.40	2*20P	48.26	50.80	2*30P	73.66	76.20	2*40P	99.06	101.60

产品编号/Product No



1: 产品类别/Product Category  
PH: 排针  
FH: 排母

2: 产品流水号/Product Serial Number  
18: 双排插件

3: 产品间距/product spacing  
127-1. 27mm  
200-2. 00mm  
254-2. 54mm

4: 产品PIN位/Product PIN position  
22P-2\*2P

5: 上针长度/upper needle length  
C60: 6.0mm

6: 下针长度/needle penetration depth  
D30: 3.0mm

7: 塑胶高度/plastic height  
G1-1.0 G2-1.5  
G3-2.0 G4-2.54

8: 包装方式/packaging method  
P-袋装/PE B-盒装/BOX  
T-管装/Tubing W-卷带/winding



9: 电镀规格/plating specifications  
T0:GF T1:1U  
T3:3U T5:5U

致力于连接器国产化  
树立智能产业新标杆



产品订购号示意图/Schematic diagram of product order number

Schematic diagram of product ordering part numbers:LCK-PH18-25422PC60D30-G4PT0

产品外形尺寸图/Outline dimension drawing of product




线路图/Circuit diagram





RECOMMEND P. C. B LAYOUT  
PCB TOLERANCE: ±0.05 (TOP VIEW)

Series Needle arrangement 排针系列



致力于连接器国产化 树立智能产业新标杆



产品



3#胶袋: 16\*18cm



纸箱