









RoHS Compliant



PIN ASSIGNMENTS

A1	GND	B9	VBUS
A5	CC1	B5	CC2
A12	GND	B4	VBUS
	SIGNAL NAME		SIGNAL NAME



NOTE:

备注:

1.MATERIAL SPECIFICATION:

1.材料规格:

1-1.HOUSING:HIGH TEMPERATURE RESISTANT PLASTIC,UL94 V-0.

1-1. 胶壳材料: 高温塑胶, 防火等级UL94 V-0

1-2.TERMINAL: COPPER ALLOY

1-2. 端子材料: 铜合金

1-3.FRONT SHELL: STAINLESS STEEL

1-3. 外壳材料: 不锈钢

2.PLATING SPECIFICATION:

2.电镀规格:

2-1.TERMINAL:

2-1. 端子:

Ni 50u" MIN. UNDER PLATED OVER ALL.

镀镍底 50u" MIN.

Au PLATED 0.5~1u" OVER Ni

表面刷金0.5~1u"

2-2.FRONT SHELL:

2-2. 外壳:

Ni 50u" MIN. PLATED OVER ALL.

镀镍底 50u" MIN.

3.MECHANICAL PERFORMANCE,

3.机械性能:

3-1.INSERTION FORCE: 0.5~2.0kgf.

3-1. 插入力: 0.5~2.0kgf.

3-2.REMOVAL FORCE: 0.6kgf~2.0kgf.

3-2. 拔出力: 0.6kgf~2.0kgf.

3-3.DURABILITY: 3000 CYCLES.

3-3. 插拔寿命: 3000 次

4.ELECTRICAL PERFORMANCE,

4.电气性能:

4-1. VOLTAGE RATING: 5.0V DC/AC

4-1. 额定电压: 5.0V DC/AC

CURRENT RATING: 3.0A

额定电流: 3.0A

4-2. LLCR: 40mΩ/PIN MAX.

4-2. 接触阻抗: 40mΩ/PIN MAX.

4-3.INSULATION RESISTANCE: 100MΩ MIN

4-3. 绝缘阻抗: 100MΩ MIN

4-4.DIELECTRIC WITHSTAND VOLTAGE,AC 100V FOR 1 MINUTE.

4-4. 耐电压: AC 100V FOR 1 MINUTE.

5. ENVIRONMENTAL PERFORMANCE:

5. 环境特性:

OPERATING TEMPERATURE: -25°C~+85°C.

工作温度: -25°C~+85°C.

RECOMMEND P.C.B LAYOUT(COMPONENT SIDE)

TOLERANCE FOR PCB LAYOUT IS ± 0.05

深圳市敏连达科技有限公司
Shenzhen Minlianda Technology Co.,Ltd.

单位(UNIT): MM

比例(SCALE) 1:1

图号(DWG NO)

未注公差
TOLERANCE UNSPECIFIED

X.X ± 0.38

X.XX ± 0.20

X.XXX ± 0.10

X" ± 5"

X.X" ± 2"

版次(REV): A/0

模号(MODEL NO)

图号(DWG NO)

品名(ITEM NO) USB TYPE C 6P 立贴5.5H

料号(PART NO) MLD-TYPE-C-6P-H5.5

页次(PAGE):1/1

设计(DESIGN)

审核(CHECKED)

核准(APPROVED)

柯南

邱敏

陈镇