

## Specification Sheet

Part Number: 157-00073



Friction tab inside of fir tree allows tie to sit in mount without falling out prior to installation.

Initial fir tree serves as a locating feature for assistance in blind assembly applications.

Disc feature provides anti-rattle protection in high vibration applications.

1-Pc Cable Tie/Fir Tree Mount, 8.3" Long, 0.25"– 0.28" Mounting Hole, PA66HIRHS, Black, 1000/pkg

Article Number 157-00073

Type T50RTM25E

Color Black (BK)

Quantity Per bag

Product Description Fir tree mounts with ties cables provide a secure grip in mounting holes and protect against dirt and other impurities. The mount provides low insertion and high extraction force, and slides along the cable tie for the proper orientation. This is sold as an assembly with the cable tie.

Short Description 1-Pc Cable Tie/Fir Tree Mount, 8.3" Long, 0.25"– 0.28" Mounting Hole, PA66HIRHS, Black, 1000/pkg

Global Part Name T50RTM25E-PA66HIRHS-BK

Minimum Tensile Strength (Imperial)	50.0
Minimum Tensile Strength (Metric)	222
Length L (Imperial)	8.0
Length L (Metric)	203.2
Fixation Method	Fir Tree
Identification Plate Position	none
Releasable Closure	Yes
Tie Closure	plastic pawl
Variant	Inside Serrated
Width W (Imperial)	0.19
Width W (Metric)	4.7
Bundle Diameter Min (Imperial)	0.06
Bundle Diameter Min (Metric)	1.6
Bundle Diameter Max (Imperial)	2.0
Bundle Diameter Max (Metric)	50.0
Thickness T (Imperial)	0.05

Thickness T (Metric)	1.3
Height H (Imperial)	0.05
Height H (Metric)	1.3
Panel Thickness Min (Imperial)	0.09
Panel Thickness Max (Imperial)	0.5
Panel Thickness Min (Metric)	2.3
Panel Thickness Max (Metric)	13.9
Mounting Hole Diameter D (Imperial)	0.28
Mounting Hole Diameter D (Metric)	6.25 - 7.0 mm
Mounting Hole Diameter D Min (Imperial)	0.25
Mounting Hole Diameter D Max (Imperial)	0.28
Mounting Hole Diameter D Max (Metric)	7.0
Disc Diameter (Metric)	12.6
Disc Diameter (Imperial)	0.5
Material	Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS)

Material Shortcut	PA66HIRHS
Flammability	UL 94 HB
UV Resistant (Yes/No)	No
Operating Temperature	-40°F to +212°F (-40°C to +100°C)
Reach Compliant (Article 33)	No
ROHS Compliant	Yes
Package Quantity (Imperial)	1000
Package Quantity (Metric)	1000
Customs Number	3926909988

## About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. ([www.hellermann.tyton.com](http://www.hellermann.tyton.com)).

© 2023 HellermannTyton. All Rights Reserved.

[Contact Us](#)

[RoHS/WEEE Compliance](#)

[Disclaimer](#)

[Terms and Conditions](#)