





REV	ECN	DESCRIPTION	MDF'D	DATE
1.0	/	新发行	骆志旺	2018-12-26



2ST F 003 C 029 ** 05 1 4

包装方式: TUBE PACKAGE(管装)
颜色: BLACK (黑色)
电镀码: 半金雾锡G0 = FLASH,
G2 = 3u, G3 = 5u,
G4 = 10u, G5 = 15u,

NOTE:

1.MATERIAL:

HOUSING: LCP 30% G/F UL 94V-0 ;BLACK
COVER: LCP 30% G/F UL 94V-0 ;BLACK
CONTACT(1.27): C5191R-H,T=0.30±0.01mm
CONTACT(0.8): C5191R-H,T=0.25±0.01mm
PEG: C2680R-H,T=0.30±0.01mm

2.MECHANICAL:

MATING: 25N MAX.
WITHDRAWAL FORCE: 5N MIN.
DURABILITY: 500 CYCLES.

3.ELECTRICAL:


CURRENT RATING: 1.5 A
CONTACT RESISTANCE:30 Milliohms MAX.
INSULATION RESISTANCE: 1000 Megohms MIN.
WITHSTANDING VOLTAGE: 500 VAC

4.FINISH:

CONTACT: 1u" GOLD MIN. PLATING ON CONTACT AREA
100u"MIN. TIN PLATING ON SOLDER TAILS
50u" MIN. NICKEL UNDERPLATING OVER ALL
PEG:100u" MIN. TIN PLATING ON SOLDER AREA
50u" MIN.NICKEL UNDERPLATING OVER ALL


5.ENVIRONMENTAL:

OPERATURE RANGE:-25°C TO +85°C



RECOMMENDED P.C.B LAYOUT

. X	±0.30	. X°	±1.0°	东莞市文章济美电子有限公司		
. XX	±0.25	. XX°	±0.5°			
. XXX	±0.20	. XXX°	±0.2°	Part Name: SAS 29PIN 母座180° DIP双排(B型)新鱼叉		
Part No. : 5001-2STF003C029G40514-B				Approved:		
Title:				Checked:		
Material:				Drawn: 骆志旺		
Mode NO. :				Date: 2018/12/26		
Drawing No. :						



SCALE 1:1 UNIT mm

PAGE: 1/1 REV: 1.1