



HC-5557-T-05



HC-5557-T-A-05 (低脚)

HC-5557-T-B-05 (高脚)

HC-5557-T-C-05 (高脚)



SPECIFICATIONS

- 1、Current Rating: 9A AC, DC
- 2、Voltage Rating: 300V AC, DC
- 3、Temperature Range: $-40^{\circ}\text{C} \sim +105^{\circ}\text{C}$
- 4、Contact Resistance: $20\text{m}\Omega$ Max
- 5、Insulation Resistance: $1000\text{m}\Omega$ Min
- 6、Withstanding Voltage: 1500V AC/minute
- 7、Material: Phosphoric brass Tin-plated
- 8、Applicable Wire Sizes: AWG #28~14#
Insulation O.D. = $0.9 \sim 3.1\text{mm}$

TYPE	Dimension mm				适用线规 AWG#
	A1	B1	A2	B2	
HC-5557-T-A-05 (低脚)	2.0	2.5	1.5	1.5	24-28
HC-5557-T-05	3.9	3.7	2.1	2.25	18-24
HC-5557-T-B-05 (高脚)	3.9	4.4	2.1	2.7	16-24
HC-5557-T-C-05 (高脚)	4.1	4.4	3.1	3.5	14-18



GENERAL TOLERANCE			制图 DRAWING		深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO., LTD			
DIM TOL			审核 CHECK		产品名称 TITLE	5557 (4.20) 端子	版本 REV.	A
X.X ± 0.30			批准 APPROVAL		产品料号 PART NO.	HC-5557-T-05	单位 UNITS	mm
X.XX ± 0.20			比例 SCALE		材料 MATERIAL		页次 SHEET	1/1
X.XXX ± 0.10			投影 Projection					
Angle $\pm 3.0^{\circ}$								
1	初版发行							
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE						