







RECOMMENDED PCB LAYOUT



SIGN	DATE	DESCRIPTION	APPROVER
△	08/26'09	Poles is changed from 2p-24p to 4p-24p	Aaron
△	08/26'09	Delete is ' VDE"	Aaron
△	08/26'09	Screw is changed from M2.5 to M3	Aaron
△	10/15'10	view revision	Aaron

THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!

Material

- Item 1 Terminal housing: Thermoplastic (UL 94V-0)
- Item 2 Clamp: Brass ,Ni plated
- Item 3 Wire guard solder pin: Brass ,Tin plated
- Item 4 Terminal screw: Steel Zinc plating"-slot type

Electrical cULus △

- Voltage rating: 300VAC
- Current rating: 10A
- Wire range:
- Solid wire(AWG): 16-26
- Stranded wire(AWG): 16-26
- Torque: 3.5Lb-In
- Screw: M3
- Wire strip length: 5-6mm
- Withstanding Voltage: 1.6KV
- Operating temperature: -40°C to +115°C
- Soldering temperature: 250°C±10°C/5 Sec
- Safety Approval: (FW 2)

TO xx 01 x 1 xxxx G

No. of poles		RoHS Pb<40,000ppm
△ 04 4 POLES	0 Black (RAL9005)	0000:"@ "Logo (Standard)
05 5 POLES	2 Red (RAL3001/D)	000A:"ANYTEK" Logo
...	3 Orange(RAL2011/P)	Any special item by
24 24 POLES	4 Yellow(RAL1018/A)	customer request,
	5 Green(RAL6018/T)	please contact sales
	6 Blue (RAL5015/A)	department.
	8 Grey(RAL 7035/D)	

Poles			04	05	06	07	08	09	10	11	12	13
Dim L			20.00	25.00	30.00	35.00	40.00	45.00	50.00	55.00	60.00	65.00
Dim B			15.00	20.00	25.00	30.00	35.00	40.00	45.00	50.00	55.00	60.00
TOL			±0.15			±0.25						
Poles	14	15	16	17	18	19	20	21	22	23	24	
Dim L	70.00	75.00	80.00	85.00	90.00	95.00	100.0	105.0	110.0	115.0	120.0	
Dim B	65.00	70.00	75.00	80.00	85.00	90.00	95.00	100.0	105.0	110.0	115.0	
TOL	±0.35			±0.40								

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		T0 5.0mm Series "- Solid block (4P-24P)									
PART NO.		T0xx01x1xxxxG				DWG NO.		8T00102			
APPROVED		CHECKED	DESIGNED	DRAWN	CUST NO.					Tolerance	
			Aaron 2010.10.15	Aaron 2009.08.26			UNIT: mm		X. ±0.50		
							SCALE: NONE		X.X ±0.30		
					SHEET: 01/01		REV: D		X.XX ±0.10		
									X° ±1°		