




K16-3K-28M

表面安装肖特基二极管
反向电压 40 ~ 200 V
正向电流 1.0 A

Surface Mounted Schottky Barrier Rectifiers
Reverse Voltage 40 ~ 200 V
Forward Current 1.0 A



特征 Features

- 反向漏电流低 Low reverse leakage
- 正向浪涌承受能力强 High forward surge capability
- 高信赖性 High reliability
- 高温焊接保证 High temperature soldering guaranteed:
260°C/10 秒
260°C/10seconds
- 引线 and 管体皆符合RoHS标准
Lead and body according with RoHS standard

机械数据 Mechanical Data

- 封装外形:SOD123FL 塑封 Case:SOD123FL Molded plastic
- 环氧树脂 : UL易燃等级 : 94V-0
Epoxy: UL 94V-0 rate flame retardant
- 引脚 : 镀锡,无铅 Lead: Pure tin plated, lead free

极限值和温度特性 TA = 25°C 除非另有规定。 Maximum Ratings & Thermal Characteristics

Ratings at 25°C ambient temperature unless otherwise specif

参数 Parameter	符号 Symbols	K16-3K-28M	单位 Unit
最大可重复峰值反向电压 Maximum repetitive peak reverse voltage	V_{RRM}	60	V
最大均方根电压 Maximum RMS voltage	V_{RMS}	42	V
最大直流阻断电压 Maximum DC blocking voltage	V_{DC}	60	V
最大正向平均整流电流 Maximum average forward rectified current	$I_{F(AV)}$	1.0	A
正向不重复浪涌电流 8.3 ms单一正弦半波 Non-repetitive peak forward surge current 8.3 ms singlehalf sine-wave	I_{FSM}	30	A
典型热阻 Typical thermal resistance (Note 1)	$R_{\theta JA}$	180	°C/W
工作结温 Operating junction temperature range	T_J	-55 --- +150	°C
存储温度 Storage temperature range	T_{STG}	-55 --- +150	°C
最大正向电压 @IF=1.0A Maximum forward voltage	V_F	0.70	V
最大反向电流 @VDC TA = 25°C Maximum reverse current	I_R	30	μA

备注 Note:


- 安装在覆铜面积5.0毫米*5.0毫米的PCB板上，从PN结到周围环境的热阻。
- Thermal resistance from junction to ambient, PCB mounted with 5.0mm*5.0mm Copper Pad Areas.



特性曲线 Characteristic Curves


正向特性曲线 (典型值)

TYPICAL FORWARD CHARACTERISTIC




正向电流降额曲线

FORWARD CURRENT DERATING CURVE



浪涌特性曲线 (最大值)

MAXIMUM NON REPETITIVE
PEAK FORWARD SURGE CURRENT



反向特性曲线

TYPICAL REVERSE CHARACTERISTICS

