


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION – –, .
© COPYRIGHT – TE Connectivity ALL RIGHTS RESERVED.


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	C	REVISED PER ECO–18–008015	24MAY2018	AP	DG





RECOMMENDED PCB LAYOUT
TOLERANCE IS ±0.05





NOTES:

HOUSING:PBT+GF(UL94V–O) BLACK
CONTACT:PHOSPHOR BRONZE
" GOLD PLATING ON CONTACT AREA
100u" MATTE TIN PLATING ON SOLDERTAIL
50u" NICKEL UNDERPLATED OVERALL

HOLDDOWN:BRASS,100u" TIN OVER 50u" NICKEL
SHELL:SPCC,50u" NICKEL PLATED
RIVET:BRASS,50u" NICKEL PLATED

LOT NUMBER "XXXX"
– STANDS FOR CALENDAR YEAR
– STANDS FOR WEEK NUMBER

YES	Au Flash	2311767-1
SCREWLOCK	Contact Area Plating	P/N

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm [INCHES]

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ± –
1 PLC ± –
2 PLC ± 0.25
3 PLC ± –
4 PLC ± –
ANGLES ± –

MATERIAL –
FINISH –

DWN AJITH PAI 22FEB2017
CHK DANIEL GORENC 22FEB2017
APVD DANIEL GORENC 22FEB2017
PRODUCT SPEC 108–130023
APPLICATION SPEC —
WEIGHT

TE Connectivity

NAME AMPLIMITE RECEPTACLE, HD22, RIGHT ANGLE, 15P
–
–

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A2	00779	C-2311767	—

CUSTOMER DRAWING | SCALE 3:1 | SHEET 1 OF 1 | REV C

2311767