


SIGN	DATE	DESCRIPTION	APPROVER
1	09/14'09	Wire guard solder pin is changed from Brass to Copper	Aaron
2	10/20'09	Part NO. is changed	Aaron
3	2010.05.31	Torque is changed from 8.9Lb-in to 5.2Lb-in	Chen Bo
4	2010.05.31	The design is changed	Chen Bo
5	2010.08.11	Clamp is changed	Chen Bo
6	2011.03.01	Add is cULus and Torque is changed	Juany
7	2011.04.02	Add is spec.	Runner
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			




N = Number of poles
Dim A=Nx6.35
Dim B=(N-1)x6.35

Poles	Dim A	Dim B
2-6p	±0.20	±0.15
7-12p	±0.30	±0.25
13-16p	±0.40	±0.35





SECTION C-C



PCB. LAYOUT

Material:

- Item a Terminal housing:Thermoplastic (UL 94V-0)
- Item b Clamp: Brass Ni plated
- 1 Item c Wire guard solder pin (Back single row): Copper Tin plated
- 1 Item d Wire guard solder pin (Front single row): Copper Tin plated
- Item e Terminal screw: Steel Zinc plating"-"slot type

Electrical

- Voltage rating: 600VAC
- Current rating: 30A
- Wire range:
- Solid wire(AWG): 10-24
- Stranded wire(AWG): 10-24
- 6 Torque(Lb-In): 5.3
- Screw: M3.5
- Wire strip length: 8-9mm
- Withstanding Voltage: 2.2KV
- Operating temperature: -40°C to +115°C
- Soldering temperature: 250°C±10°C/5 Sec
- 6 Safety Approval: c UL us

2 KP xx 0 1 x 0 xxxx G → RoHS Pb<40,000ppm

No. of poles end stackable design		0	Black (RAL9005)
02	2 CONTACTS	2	Red (RAL3001/D)
03	3 CONTACTS	3	Orange(RAL2011/P)
...	...	4	Yellow(RAL1018/A)
16	16 CONTACTS	5	Green(RAL6018/T)
		6	Blue (RAL5015/A)
		8	Grey(RAL7035/D)

0000 Standard @ Logo
000A Standard ANY Logo
Any special item by customer request, please contact sales department.

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	KP 6.35 Series Solder pins staggered by half pin spacing (without cover)				
PART NO.	KPxx01x0xxxxG 2			DWG NO.	8KP0004
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.	
		Runner 2011.04.02	Chen Bo 2010.08.11	UNIT: mm / SCALE: NONE / SHEET: 01/01 / REV.: H	

Tolerance	
X.	±0.50
X.X	±0.30
X.XX	±0.10
X°	±1°