

## Features

- rugged welded case, hermetic
- other standard and custom PLP models available with wide selection of fco

## Applications

- test equipment
- lab use
- transmitters/receivers
- military/hi-rel applications

## HT-PLP-90+



50Ω DC to 81 MHz

### Maximum Ratings

Operating Temperature -55°C to 100°C

Storage Temperature -55°C to 100°C

RF Power Input\* 0.5W max.

Permanent damage may occur if any of these limits are exceeded.


### Low Pass Filter Electrical Specifications (T<sub>AMB</sub>= 25°C)

PASSBAND (MHz)	fco (MHz) Nom.	STOPBAND (MHz)		VSWR (:1)	
		(Loss>20dB)	(Loss>40dB)	Passband Typ.	Stopband Typ.
(loss < 1 dB)	(loss 3 dB)				
DC-81	90	121-157	157-400	1.7	18


### Typical Performance Data at 25°C

Frequency (MHz)	Insertion Loss (dB)		Return Loss (dB)	Frequency (MHz)	Group Delay (nsec)
	x	σ			
1.00	0.05	0.1	42.0	1.00	9.672
12.50	0.14	0.1	37.5	12.50	9.503
24.00	0.18	0.1	27.7	24.00	9.491
35.50	0.31	0.1	18.7	35.50	9.776
46.50	0.42	0.1	14.9	46.50	10.240
58.00	0.43	0.1	16.1	58.00	11.244
81.00	0.69	0.1	17.0	81.00	15.573
87.00	1.28	0.4	9.7	84.00	17.894
90.00	2.01	0.5	7.6	87.00	19.997
93.00	6.43	0.9	3.8	90.00	24.263
97.00	8.74	1.0	1.7	93.00	21.734
104.01	12.94	1.1	0.8	97.00	17.532
111.00	16.72	1.2	0.5	104.00	15.893
115.52	21.91	1.2	0.1	111.00	12.218
121.03	26.16	1.2	0.2	115.50	5.804
130.03	32.40	1.3	0.3	121.00	5.229
140.04	38.50	1.4	0.3	130.00	3.892
145.04	41.31	1.4	0.3	135.00	2.740
150.04	43.98	1.5	0.3	140.00	0.487
155.05	46.76	1.7	0.3	145.00	0.841
157.05	47.69	1.8	0.3	150.00	2.060
184.06	60.11	2.9	0.3	155.00	7.687
206.57	66.87	1.4	0.3	157.00	5.680
229.58	75.03	5.6	0.2	184.00	5.380
252.57	74.83	7.6	0.2	195.50	5.060
298.08	76.96	7.1	0.1	206.50	4.470
321.08	75.07	4.9	0.1	218.00	4.320
355.57	73.10	4.4	0.1	229.50	4.010
378.08	75.50	4.8	0.1	241.00	3.760
400.07	74.56	6.3	0.1	252.00	3.450

### electrical schematic




### typical frequency response



### Pad Connections

INPUT	1
OUTPUT	8
GROUND	2,3,4,5,6,7
CASE GROUND	2,3,4,5,6,7

### Outline Drawing



### Outline Dimensions: Unit ( mm )

A	19.56	B	20.32	C	9.78
D	10.16	E	9.40	F	10.16
G	5.08	H	5.08	J	3.56
K	0.79	wt		5.2	

