



REV.	DESCRIPTION	ECN NO.	NAME	DATE

1  
2  
3  
4  
5




**SPECIFICATIONS**



Current Rating: 1.5 Amps  
 Insulation Resistance: 1000M $\Omega$  Min  
 Contact Resistance: 20m $\Omega$  Max  
 Withstanding Voltage: AC 500V  
 Operation Temperature: -40 $^{\circ}$ to+105 $^{\circ}$   
 Contact Material: Brass  
 Standard: PA6T  
 Insulator Material: Polyester(UL 94V-0)  
 Contact Plating: Gold Flash  
 Max.Processing Temp: 240 $^{\circ}$ C for30-60seconds  
 (260 $^{\circ}$ C for 5 seconds)



RECOMMEND P.C.B LAYOUT  
 PCB TOLERANCE:±0.05 (TOP VIEW)



P/N	PIN	DIM.A	DIM.B
PM-2.0-1*01-4.3-ZZ	1	0.00	2.00
PM-2.0-1*02-4.3-ZZ	2	2.00	4.00
PM-2.0-1*03-4.3-ZZ	3	4.00	6.00
PM-2.0-1*04-4.3-ZZ	4	6.00	8.00
PM-2.0-1*05-4.3-ZZ	5	8.00	10.00
PM-2.0-1*06-4.3-ZZ	6	10.00	12.00
PM-2.0-1*07-4.3-ZZ	7	12.00	14.00
PM-2.0-1*08-4.3-ZZ	8	14.00	16.00
PM-2.0-1*09-4.3-ZZ	9	16.00	18.00
.....	.....	.....	.....
PM-2.0-1*40-4.3-ZZ	40	(PIN-1)x2.0	(PIN)x2.0

GENERAL TOLERANCE		DONGGUAN BAOXUN PRECISION TECHNOLOGY CO., LTD				 	
DIM.	TOL.	TITLE: 2.0FH H4.3 1xnPin 180度 W2.4 U型 PC2.8 6T					
x.	±0.30	DWG. NO.: PM-2.0-1*N-4.3-ZZ		CHECKED: MAX			
x.x	±0.20	PART NO.: PM-2.0-1*N-4.3-ZZ		DRAWN: ELLA			
x.xx	±0.10	UNIT: mm		SCALE: none	SHEET: 1 of 1		
GENERAL ANGLE:		DWG. SIZE: A4	LAYER: bxconn	APPROVED: WILL			
x $^{\circ}$	±5'						
x.x $^{\circ}$	±1'						
x.xx $^{\circ}$	±0.5'						