深圳市首韩科技有限公司
SHENZHEN SHOUHAN TECHNOLOGYCO.,LTD
Tel: 0755-27597601 Fax: 0755-27597491

承 认 书
SPECIFICATION FOR APPROVAL

客 户 Customer：

产品名称 Project： 电感

规格型号 Part No： CYA0520-6.8UH

贵公司承认印 Approval signatures

料 号/Part No.	签 章/Signatures

日期 Date:

拟制/Drawn	李春风	深圳市首韩科技有限公司 工程专用章
审核/Check	钟华华	
批准/Approved	罗孝金	

深圳市首韩科技有限公司


1.Features

①. High performance (Isat) realize by metal dust core.
②. Low profile: Thickness max.2.0～5.0mm.
③. Low loss and low resistance.
④. Capable of corresponding high frequency 1MHz～5MHz.
⑤ Ultra low buzz noise, due to composite construction.
⑥. The products contain no lead and also support lead-free soldering.

2.Applications area


Ideally used in NB/Desktop/server/Graphic card, LCD TV/Projector, etc as DC-DC Converter.

3. Externl Dimensions (unit: mm)



UNIT: mm
A:5.7±0.3
B:5.2±0.3
C:2.0MAX
D:2.3±0 .2
E:1.1±0.3

4. Product Code



Code 代码	Tolerance 公差
J	±5%
K	±10%
L	±15%
M	±20%
P	±25%
N	±30%

• 电感值Inductance Value
(1R0:1.0uH; 100: 10uH; 101:100uH)

深圳市肯韩科技有限公司

5. Electrical Characteristics

CYA0520 Series

Electrical Characteristics						
C.Y PART NO	L0(uH) Inductance (uH）@（0A)	Rdc (mΩ) @25°C		Heat Rating Current DC Amps. Idc (A)	Saturation Current DC Amps. Isat（A)	TEST FREQ (KHZ)
		Typ.	Max.			
CYA0520-1R0M	1.0±20%	16.00	20.00	6.00	9.00	100KHZ/1.0v
CYA0520-1R5M	1.5±20%	26.00	35.00	5.50	6.50	100KHZ/1.0v
CYA0520-2R2M	2.2±20%	32.00	45.00	4.00	6.00	100KHZ/1.0v
CYA0520-3R3M	3.3±20%	72.00	80.00	3.50	5.00	100KHZ/1.0v
CYA0520-4R7M	4.7±20%	86.00	95.00	3.00	4.00	100KHZ/1.0v
CYA0520-6R8M	6.8±20%	116.00	130.00	2.80	3.50	100KHZ/1.0v
CYA0520-100M	10.0±20%	152.00	180.00	2.30	2.80	100KHZ/1.0v

深圳市首韩科技有限公司

- **Notes**


1.All test data is reference to 25℃ ambient.
2.Idc: DC current (A) that will cause an approximate △T of 40℃
3. Isat ： DC current (A) that will cause L0 to drop approximately 30%
4.Operating Temperature Range -55℃ to +125℃
5.The part temperature (ambient + temp rise) should not exceed 125 ℃ under worse case operating conditions. Circuit design, component. PWB trace size and thickness airflow and other cooling provisions all affect the part temperature. Part temperature should be verified in the den application.

6.The rated current as listde is either the saturation current or the heating current depending on which value is lower.

6.Minimum Packaging and storage

- 包装**Packing**

Tape Dimension




Type	Reel Dimensions（mm）				Tape Dimensions（mm）						
	A	N	W	C	W	P	P0	A0	B0	H	T
CYA0420	330 +2/-0	100 +2/-0	12.4 +2/-0	13.2 ±0.2	12±0.3	8±0.1	4±0.1	4.4±0.1	4.9±0.1	2.3±0.05	0.35±0.05
CYA0530	330 +2/-0	100 +2/-0	12.4 +2/-0	13.2 ±0.2	12±0.3	8±0.1	4±0.1	5.4±0.1	5.9±0.1	3.3±0.05	0.35±0.05
CYA0618	330 +2/-0	100 +2/-0	16.4 +2/-0	13.2 ±0.2	16±0.3	12±0.1	4±0.1	6.9±0.1	7.5±0.1	2.1±0.05	0.35±0.05
CYA0624	330 +2/-0	100 +2/-0	16.4 +2/-0	13.2 ±0.2	16±0.3	12±0.1	4±0.1	6.9±0.1	7.5±0.1	2.7±0.05	0.35±0.05
CYA0630	330 +2/-0	100 +2/-0	16.4 +2/-0	13.2 ±0.2	16±0.3	12±0.1	4±0.1	6.9±0.1	7.5±0.1	3.3±0.05	0.35±0.05
CYA0650	330 +2/-0	100 +2/-0	16.4 +2/-0	13.2 ±0.2	16±0.3	12±0.1	4±0.1	6.9±0.1	7.5±0.1	5.2±0.1	0.4±0.05
CYA0850	330 +2/-0	100 +2/-0	24.4 +2/-0	13.2 ±0.2	12.0±0.1	24.0±0.3	4±0.1	8.5±0.1	10±0.1	5.25±0.1	0.4±0.05
CYA1040	330 +2/-0	100 +2/-0	24.4 +2/-0	13.2 ±0.2	24±0.3	16±0.1	4±0.1	10.4±0.1	11.5±0.1	4.3±0.1	0.35±0.05
CYA1250	330 +2/-0	100 +2/-0	24.4 +2/-0	13.2 ±0.2	24±0.3	16±0.1	4±0.1	13.2±0.1	14.4±0.1	5.3±0.1	0.4±0.05
CYA1260	330 +2/-0	100 +2/-0	24.4 +2/-0	13.2 ±0.2	24±0.3	16±0.1	4±0.1	13.2±0.1	14.4±0.1	6.3±0.1	0.5±0.05

深圳市首韩科技有限公司

• **Tape Carrier Packaging**:

Type	Standard Quantity (pcs/reel)	Type	Standard Quantity (pcs/reel)
CYA0420	**3000**	CYA0850	**1000**
CYA0530	**2000**	CYA1040	**1000**
CYA0630	**1000**	CYA1250	**500**
CYA0650	**1000**	CYA1265	**500**

• **Recommended reflow soldering curve**



• **Application Notice**

Storage ConditionsTo maintain the solderability of terminal electrodes:

1. Temperature and humidity conditions: Less than 30℃ and 70% RH.
2. Recommended products should be used within 6 months form the time of delivery.
3. The packaging material should be kept where no chlorine or sulfur exists in the air.

Transportation

1. Products should be handled with care to avoid damage or contamination from perspiration and skin oils.
2. The use of tweezers or vacuum pick up is strongly recommended for individual components. Bulk handling should ensure that abrasion and mechanical shock are minimized.

深圳市昌精科技有限公司