

SIGN	DATE	DESCRIPTION	APPROVER
△	02/01'07	Soldering temperature is changed from 245°C to 250°C	Marivn
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			

Material

- Item① Terminal body(metal housing): Brass(CuZn),Tin plated
- Item② Terminal screw: Steel Zinc plating "-" slot type
- Item③ Wire guard: Stainless steel
- Item④ Insulator (housing): Thermoplastic (UL94V-0)

Electrical

- Voltage rating: 300VAC
- Current rating: 15A
- Wire range:
- Solid wire(AWG): 14-24
- Stranded wire(AWG): 14-24
- Torque(Lb-In): 3.5
- Screw: M2.6
- Wire strip length: 5-6mm
- Withstanding Voltage: 1.6KV
- Operating temperature: -40°C to +115°C
- △ ● Soldering temperature: 250°C±10°C/5 Sec


T9 xx 21 x 0 xxxx G

02	2 CONTACTS	0	Black	0000: "@" Logo	RoHS
03	3 CONTACTS	5	Green	000A: "ANYTEK" Logo	Pb<40,000ppm
...	...	6	Blue	Any special item by customer request. please contact sales department.	
24	24 CONTACTS	8	Grey		

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	T9 - 5.08mm Series "-"				DWG NO.		8T90001	
PART NO.	T9xx21x0xxxxG				DWG NO.		8T90001	
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.			Tolerance	
	Marvin 2007.04.12	Marvin 2007.04.12	Marvin 2007.04.12				UNIT: mm	X. ±0.50
							SCALE: NONE	X.X ±0.30
								X.XX ±0.10
								X° ±1°
					SHEET: 01/01		REV.: C	

