Johanson Part Number TCCP250W105K1GV001T

Johanson Part Number: TCCP250W105K1GV001T	Johanson Company: JDI
Legacy P/N: 250R14W105KV4T	Size for Capacitors (EIA): 0603
Description: Capacitors Tanceram, X7R, 0603, 25V, 1µF±10%, Ni/Sn (RoHS), 7" Reel Paper Tape	Specification Number: None
Life Cycle Stage: Active: China Ship-To Only - EOL rest of the world	NCNR: No
AEC Q200 Qualified: No	Thickness (Max): 0.035
Schedule B: 8532.24.00.20	Thickness (Min): None
ITAR: No	End Band(Min): 0.01
ECCN: EAR99	End Band (max): 0.015
RoHS Compliance: Yes, RoHS 10/10	Standard Item: Yes
REACH: Yes	Lead Time Typical (Weeks)*: 22
Country of Origin: CN	Length (Min): 0.055
Product Family: Capacitors	Length (Max): 0.071
Product Subfamily: Capacitors Tanceram Hi-Cap	Width (Min):0.024
Capacitance Value: 1.000	Width (Max): 0.040
Cap Unit of Meas: µF	Part Weight (mg): None
Tolerance: ±10%	Packaged Width (lb) Arm: None
Voltage: 25.0	Packaging: 7" Reel Paper Tape
Dielectric Temp Coefficient: X7R	Packaging Qty: None
Termination: 68	Operating Temp Range: -55°C to +125°C
Marking: No Mark	Storage Temp Range (Packaged): +5°C to +40°C with RH 20% to 70%
Product Release Date: Jan. 3, 2006	Storage Temp Range (None Operating): -65°C to +125°C
Harmonization: 8532.24.00.20	

*This can vary significantly so it is important to obtain a quotation with lead time for production planning purposes.

Web Page Link: https://www.johansondielectrics.com/tanceram-capacitors

Printed from: https://www.johansontechnology.com/part/TCCP250W105K1GV001T/