

SHEET 1 OF 1




RECOMMENDED PANEL CUT-OUTS







▲ SWITCH FUNCTION		
POS. 1	POS. 2	POS. 3
		
ON	OFF	(ON)
1-2, 4-5	OPEN	(2-3), (5-6)

(ON) = MOMENTARY







NOTES:
1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X = ±0.4
   X.XX = ±0.25
3. TERM. NUMBERS FOR REF. ONLY
▲4. RATING: 16(8)A 125/250VAC µT55
5. ELECTRICAL LIFE: 10,000 CYCLES
6. CONTACT RESISTANCE: <20 MILLI-OHMS INITIAL
7. DIELECTRIC STRENGTH: >1,500V AC 1MIN
8. INSULATION RESISTANCE: >100MOHMS
9. OPERATING TEMP: -10°C to 55°C
10. INGRESS PROTECTION: IP68
11. ▲ DENOTES CRITICAL PARAMETER.
12. SUPPLIED HARDWARE: LOCK WASHER and TWO HEXNUTS

REV	ECO NO	DESCRIPTION	DATE	BY
A	ECO-101110	Release	07/15/22	MW

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

E-SWITCH®

OBJECT ID 100122325

TITLE ST4DP9AT1S2

SCALE	DATE	DR	DWG	REV
1:1	7/11/2022	MW	14-ST4DP9AT1S2	A