35772 ✔ ACTIVE

SOLISTRAND

TE Internal #: 35772

Closed Ring Tongue Terminal, 12 – 10 AWG, 1/4 / M6 Stud, 6.73 mm [.265 in] Stud Diameter, Closed Barrel, Straight, Tin Plating, Uninsulated

View on TE.com >

Terminals & Splices > Ring Terminals







Ring Terminal Product Type: **Closed Ring Tongue Terminal**

Wire Size: **5180 – 13100 CMA**

Stud Size: **1/4, M6**

Features

Configuration Features

Number of Holes	1

Body Features

Product Weight	1.735 g

Mechanical Attachment

Wire Insulation Support	Without

Industry Standards

Government Qualified Terminal	No

Packaging Features

Packaging Quantity	500
Packaging Method	Loose Piece

Product Type Features

Ring Terminal Product Type	Closed Ring Tongue Terminal
Stud Size	1/4, M6
Sealable	No
Wire Insulation Support Retention Type	Non-Insulation Support

Contact Features

Barrel Type	Closed
Terminal Orientation	Straight
Terminal Plating Material	Tin

Dimensions

Wire Size	5180 – 13100 CMA
Stud Diameter	6.73 mm[.265 in]
Tongue Thickness	.99 mm[.04 in]
Product Length	21.97 mm[.86 in]
Barrel Inside Diameter	3.28 mm[.129 in]

Usage Conditions

Insulation Option	Uninsulated

Operation/Application

Compatible With Wire Base Material	Copper
Compatible With Wire Plating Material	Tin

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

Compatible Parts



TE Part # 58545-3
SDE DIE ASSY. 22-10 SOLISTRAND



TE Part # 58545-1
SOLISTRAND 10-22 DIE ASSY



TE Part # 525693
DAHT SOLIS 22-10 ASSY




TE Part # 49935
DAHT SOLIS 22-10 ASSY



TE Part # 169400
CERTI-LOK FRAME W/O DIES



TE Part # 58546-1
PC 22-10 SOLISSPICE SPL I SHT



TE Part # 47814
DIES SOLIS 12-10 DIE SET



TE Part # 1-1377172-3
SMP 0-0035772-0

Customers Also Bought



TE Part #323127
SOLIS SPD 22-16COMM 22-18MIL 6




TE Part #1437653-7
6PCV-07-006=6PCV ASSEMBLY



TE Part #1825096-1
TPA11CGPC004



TE Part #8-1437652-3
6PCV-05-008=#6TRIBARRIER TERMI




TE Part #4-1617752-5
FCA-215-HZ4



TE Part #330827
TERMINAL,SOLIS SPD 16-14 6



TE Part #322439-003
RCAB-5120



TE Part #565915-018
IXSU-F3151

TE Part #1825219-4
TT11DGRA104

TE Part #EN0127-000
SMOE-64623

Documents

Product Drawings

TERMINAL,SOLIS R 12-10 1/4

English

CAD Files

Customer View Model

ENG_CVM_CVM_35772_K.2d_dxf.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_35772_K.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_35772_K.3d_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Instruction Sheets

Instruction Sheet (U.S.)

English

Agency Approvals

UL Report

English

UL Report

English