



2N7002ZT

Power MOSFET

300mA, 60V N-CHANNEL ENHANCEMENT MODE POWER MOSFET



DESCRIPTION

The UTC **2N7002ZT** uses advanced technology to provide excellent $R_{DS(ON)}$, low gate charge and low gate voltages during operation. This device is suitable for use as a load switch or in PWM applications.

FEATURES

- * Low Reverse Transfer Capacitance (C_{RSS} = typical 3.0 pF)
- * ESD Protected
- * Fast Switching Capability
- * Avalanche Energy Specified
- * Improved dv/dt Capability, High Ruggedness

SYMBOL




ORDERING INFORMATION

Ordering Number		Package	Pin Assignment			Packing
Lead Free	Halogen Free		1	2	3	
2N7002ZTL-AN3-R	2N7002ZTG-AN3-R	SOT-523	G	S	D	Tape Reel

Note: Pin Assignment: G: Gate S: Source D: Drain

2N7002ZTG-AN3-R		(1)Packing Type	(1) R: Tape Reel
		(2)Package Type	(2) AN3: SOT-523
		(3)Green Package	(3) G: Halogen Free and Lead Free, L: Lead Free

MARKING



■ ABSOLUTE MAXIMUM RATINGS ($T_A = 25^\circ\text{C}$, unless otherwise specified.)

PARAMETER		SYMBOL	RATINGS	UNIT
Drain-Source Voltage		V _{DSS}	60	V
Gate-Source Voltage		V _{GSS}	±20	V
Drain Current	Continuous	I _D	300	mA
	Pulse(Note 2)		800	
Power Dissipation		P _D	200	mW
Derating above T _A =25°C			1.6	mW/°C
Junction Temperature		T _J	+150	°C
Storage Temperature		T _{STG}	-55 ~ +150	°C

Note: Absolute maximum ratings are those values beyond which the device could be permanently damaged.

Absolute maximum ratings are stress ratings only and functional device operation is not implied.


■ ELECTRICAL CHARACTERISTICS ($T_A=25^\circ\text{C}$, unless otherwise specified.)

PARAMETER	SYMBOL	TEST CONDITIONS	MIN	TYP	MAX	UNIT
OFF CHARACTERISTICS						
Drain-Source Breakdown Voltage	BV _{DSS}	V _{GS} =0V, I _D =10μA	60			V
Drain-Source Leakage Current	I _{DSS}	V _{DS} =60V, V _{GS} =0V			1	μA
Gate-Source Leakage Current	I _{GSS}	V _{DS} =0V, V _{GS} =±20V			±10	μA
ON CHARACTERISTICS						
Gate Threshold Voltage	V _{GS(TH)}	V _{DS} =10V, I _D =1mA	1.0	1.85	2.5	V
Static Drain-Source On-Resistance (Note)	R _{DS(ON)}	V _{GS} =10V, I _D =0.3A, T _J =125°C			13.5	Ω
		V _{GS} =5V, I _D =0.05A			7.5	
DYNAMIC PARAMETERS						
Input Capacitance	C _{ISS}	V _{DS} =25V, V _{GS} =0V, f=1.0MHz		25	50	pF
Output Capacitance	C _{OSS}			10	25	pF
Reverse Transfer Capacitance	C _{RSS}			3.0	5.0	pF
SWITCHING PARAMETERS						
Turn-ON Delay Time	t _{D(ON)}	I _D =0.2 A, V _{DD} =30V, V _{GS} =10V,		12	20	ns
Turn-OFF Delay Time	t _{D(OFF)}	R _L =150Ω, R _G =10Ω		20	30	ns
DRAIN-SOURCE DIODE CHARACTERISTICS AND MAXIMUM RATINGS						
Maximum Continuous Drain-Source Diode Forward Current	I _S				300	mA
Maximum Pulsed Drain-Source Diode Forward Current	I _{SM}				0.8	A
Drain-Source Diode Forward Voltage	V _{SD}	V _{GS} =0V, I _S =300mA (Note)		0.88	1.5	V


Notes: 1. Device mounted on FR-4 PCB, 1 inch x 0.85 inch x 0.062 inch. Minimum land pad size.

2. Pulse width $\leq 300\mu\text{s}$, Duty cycle $\leq 1\%$

■ TEST CIRCUITS AND WAVEFORMS



Switching Test Circuit



Switching Waveforms

UTC assumes no responsibility for equipment failures that result from using products at values that exceed, even momentarily, rated values (such as maximum ratings, operating condition ranges, or other parameters) listed in products specifications of any and all UTC products described or contained herein. UTC products are not designed for use in life support appliances, devices or systems where malfunction of these products can be reasonably expected to result in personal injury. Reproduction in whole or in part is prohibited without the prior written consent of the copyright owner. UTC reserves the right to make changes to information published in this document, including without limitation specifications and product descriptions, at any time and without notice. This document supersedes and replaces all information supplied prior to the publication hereof.