


No. of pos.	A $_{-0,76}$	B $_{+0,25}$	C	Part-No.
9	31,19	16,46	25,00 $^{+0,12}_{-0,13}$	165X17209X
15	39,52	24,79	33,30 $^{+0,15}_{-0,1}$	165X17219X
25	53,42	38,50	47,04 $\pm 0,13$	165X17229X
37	69,70	54,96	63,50 $\pm 0,13$	165X17239X


(b) (c)


(5 : 1)












NOTES:

1. METALSHELLS: COPPER ALLOY; min. 315µin TIN over 40-80µin NICKEL
2. SEALING ELEMENT: TPE
3. THREADED INSERTS: COPPER ALLOY; min. 200µin TIN over 80µin NICKEL
4. JACK SCREWS: STEEL; NICKEL PLATED
5. COLLARS: COPPER ALLOY; min. 200µin TIN over 80µin NICKEL
6. MAXIMUM TORQUE VALUE FOR THREAD: 6 in.LB
7. (c) CONNECTOR IS PART MARKED: PART NO. CONEC ABC



Directive 2002/95/EC RoHS compliant

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION.
OWNERSHIP AND COPYRIGHT OF CONEC GmbH
DO NOT ALTER CAD DRAWING BY HAND

rev.	description	date	name
3 x c	Ä4774	31.07.2013	K.H.
1 x b	Ä3781	21.10.2010	K.H.
a	Original		

tolerance — dim. in mm

	date	name
drawn	10.11.05	Lehmenkühler
appd.	10.11.05	Mickenbecker
norm	DIN 41652	
d-old		

scale: 2:1 (5:1)
material: SEE NOTES

title:
HOOD 9-37pos.
WATER RESISTANT AND SHIELDED; FOR EMI/RFI
for plug connector, with jack screws

dwg no: 16K1A1548 — DIN-A3 — sh: 1

part no: SEE TABLE