MSRTA20060(A)D thru MSRTA200100(A)D

Silicon Standard Recovery Diode


V_{RRM} = 600 V - 1000 V

$I_{F(AV)}$ = 200 A

Features

- High Surge Capability
- Types from 600 V to 1000 V V_{RRM}
- Isolation Type Package
- Electrically Isolated Base Plate
- Not ESD Sensitive

Heavy Three Tower Package





RoHS COMPLIANT

REACH COMPLIANCE

Maximum ratings, at T_j = 25 °C, unless otherwise specified

Parameter	Symbol	Conditions	MSRTA20060(A)D	MSRTA20080(A)D	MSRTA200100(A)D	Unit
Repetitive peak reverse voltage	V_{RRM}		600	800	1000	V
DC blocking voltage	V_{DC}		600	800	1000	V
Operating temperature	T_j		-55 to 150	-55 to 150	-55 to 150	°C
Storage temperature	T_{stg}		-55 to 150	-55 to 150	-55 to 150	°C

Electrical characteristics, at Tj = 25 °C, unless otherwise specified

Parameter	Symbol	Conditions	MSRTA20060(A)D	MSRTA20080(A)D	MSRTA200100(A)D	Unit
Average forward current (per leg)	$I_{F(AV)}$	T_C = 125 °C	200	200	200	A
Peak forward surge current (per leg)	I_{FSM}	t_p = 8.3 ms, half sine	3000	3000	3000	A
Maximum instantaneous forward voltage (per leg)	V_F	I_{FM} = 200 A, T_j = 25 °C	1.1	1.1	1.1	V
Maximum instantaneous reverse current at rated DC blocking voltage (per leg)	I_R	T_j = 25 °C	10	10	10	µA
		T_j = 150 °C	5	5	5	mA
Thermal characteristics						
Maximum thermal resistance, junction - case (per leg)	$R_{\Theta jc}$		0.35	0.35	0.35	°C/W

Figure .1- Typical Forward Characteristics




Figure. 2 Forward Derating Curve




Figure.3-Peak Forward Surge Current







Figure .4 -Typical Reverse Characteristics



Package dimensions and terminal configuration

Product is marked with part number and terminal configuration.





DIMENSIONS					
DIM	INCHES		MM		NOTE
	MIN	MAX	MIN	MAX	
A	3.150	NOM	80.01	NOM	
B	.872	.892	22.15	22.65	
C	.465	.479	11.82	12.18	
D	1.337	1.356	33.95	34.45	
E	.230	.234	5.84	6.16	
F	.725	REF	18.42	REF	
G	3.668	3.768	93.17	95.71	
H	----	.791	---	20.10	
J	1/4-20 UNC FULL				
K	.509	.538	12.92	13.68	Ø
M	.238	.258	6.05	6.55	Ø