





RoHS

SPECIFICATIONS

Rated Current:1.5AMP
 Contact Resistance:20mΩ Max
 Withstand Voltage:500V AC/DC
 Insulation Resistance:1000MΩ Min
 Operation Temperature:-40°C to +105°C

Contact Material:Brass
 Contact Plating:Au or Sn Over Ni
 Insulator Material:Polyester(UL94V-0)
 Standard: PA6T
 Max.Processing Temp: 230°C for 30-60 seconds
 (260°C for 10 seconds)

Recommended P.C.B Layout(Top Side)
 (PCB BOARD TOLERANCE±0.05)



Dimension antitheses list					
ITEM	PB	PC	PW	H	W
001	4.6		6.2	4.3	4.0
002					

深圳市连盛精密连接器有限公司

PART NO.

1020200386

TITLE:

2.0FH H=4.3 W=4.5 2*3P SMT=6.2 总高
4.6 U型 AU1U 青铜 PA6T

OPERATION

SCALE

UNIT

FIT

X.X ±0.30

DRAW

mm

X.XX ±0.20

CHECK

SIZE

A4

X.XXX ±0.10

APPROVE

SHEET

1/1

Angle ±3°

DIM TOL

PROJ.

☐

REV

DATE

MODIFICATION DESCRIPTION

CHANGE

1

2

3

4

5

6

7

8

9