



THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION -,- .
© COPYRIGHT – TE Connectivity Ltd. ALL RIGHTS RESERVED.


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	B1	REVISED PER ECR-18-007748	26JUN2018	BDA	DH











TYCO ELECTRONICS RECOMMENDATION IS THAT THE MATING TAB MUST BE HELD TO A TOLERANCE OF ±0.13 [.005] IN EITHER DIRECTION IN ORDER TO MINIMIZE BOTH THE MAGNITUDE AND VARIATION IN INSERTION FORCE.

MATING TAB

1969202

	66 Nylon V0 Natural	1969202-2
SUPERSEDED BY 1969202-2	66 NYLON, V0	~~1969202-1~~
	MATERIAL	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm [INCHES]

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ± –
1 PLC ± –
2 PLC ± 0.25 [.010]
3 PLC ± –
4 PLC ± –
ANGLES ± 1°

MATERIAL: SEE TABLE
FINISH: NATURAL

DWN JR RUTH 11jun08
CHK PETE DESANTIS 11JUN08
APVD PETE DESANTIS 11JUN08
PRODUCT SPEC —
APPLICATION SPEC —
WEIGHT

TE Connectivity Ltd.

NAME HOUSING, RECPT, FASTON, 6.35 [.250] SERIES
—

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A2	00779	C-1969202	—

CUSTOMER DRAWING | SCALE 2:1 | SHEET 1 OF 1 | REV B1