









RoHS

MAPX	MODIFICATION	DRW	DATE

- NOTES:
- MATERIAL: SEE "TABLE 1";
 - FINISH: SEE "TABLE 1";
 - ELECTRICAL :
 - CONTACT CURRENT RATING :
3A (VBUS PIN 1.5A/PIN MAX),
3A (GND PIN 1.25A/PIN MAX), 0.25A/PIN
(OTHER PIN).
 - INSULATION RESISTANCE :
100 MEGAOHMS MIN. AT 250VDC.
 - DIELECTRIC WITHSTANDING VOLTAGE :
100VAC MIN.
 - LOW LEVEL CONTACT RESISTANCE :
INITIAL 40mΩ MAX.
AFTER 50mΩ MAX.
 - MECHANICAL CHARACTERISTICS :
 - MATING FORCE: 5~20N.;
 - UNMATING FORCE: 8~20N (INITIAL),
6~20N (AFTER 10000 CYCLES);
 - DURABILITY : 10,000 MATING CYCLES.
 - OPERATING TEMPERATURE : -40° C TO +80° C



P. C. B LAYOUT

TABLE 1:

④	Shell	1	Stainless steel	NI PLATING;	T=0.30mm
③	MID PLATE	1	Stainless steel		T=0.15mm
②	Terminal	16	C5191/C2680	半金锡	T=0.15mm
①	Housing	3	HIGH TEMP	黑色	
NO.	PART NAME	QTY	MATERIAL	DESCRIPTION	REMARK

产品图 PRODUCT CHART DWG		深圳市精拓金电子有限公司 Shenzhen Jing Tu Jin Electronics Co., Ltd.							
公差一览表 TOLERANCE UNLESS OTHERWISE		单位 UNITS	MM	制图 DRAWING	YANG	制图料号 PRODUCT PART NO.	918-418K2023S40023		
X.	±0.25	X.	±5°	比例 SCALE	1:1	产品名称 PRODUCT NAME	TYPE-C3.1母座板上7.35四脚 全贴单排SMT有柱 16PIN3A		
.XX	±0.15	.XX	±1°	日期 DATE	2020-05-22	核准 APPD	角法 VIEW	版本 VER	AD
.XXX	±0.02	.XXX	±0.5°						