



SIGN	DATE	DESCRIPTION	APPROVER
⚠1	11/12'12	change the product number	Da cheng
⚠2	11/09'13	change the electrical specification /// update the drawing	Da cheng
⚠3	12/28'13	update the drawing	Da cheng
		THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!	



SECTION A-A⚠







PCB LAYOUT
TOP VIEW

Material:
- Item ① Terminal body: Thermoplastic (UL94V-0)
- Item ② Terminal side body: Thermoplastic (UL94V-0)
- Item ③ Terminal cover: Thermoplastic (UL94V-0)
- Item ④ Solder pin(front) : Copper, Tin Plated.
- Item ⑤ Solder pin(back) : Copper, Tin Plated.
- Item ⑥ Spring clamp : Stainless steel

⚠ Electrical:	cULus
Voltage rating:	600 V
Current rating(SOL):	30 A
Current rating(STR):	40 A
Wire range:	
Solid wire(AWG):	8-20
Stranded wire(AWG):	4-20
Wire strip length:	18-19mm
Withstanding Voltage:	2.2KV
Operating temperature:	-40°C to +115°C
Soldering temperature:	260°C ±5°C/5 Sec
Safety Approval:	cULus
Critical dimension:	Ⓒ

⚠NP xx 1 1 x 2 xxxx G

⚠⚠No. OF POLES
01: 1POLES
03: 3 POLES
:
11: 11 POLES

⚠Body Color
0 Black (RAL9005)
2 Red (RAL3001/D)
3 Orange(RAL2011/P)
4 Yellow(RAL1018/A)
5 Green(RAL6018/T)
6 Blue (RAL5015/A)
8 Grey(RAL7004/P)
9 White(RAL1102)
C Multiple colors

RoHS compliant (lead<4%) In copper Alloy

0000: "@" Logo (Standard)
000A: "ANYTEK" Mark
Any special item by customer requst. please contact sales department.

⚠ N=NUMBER OF POLES

DIM		Tolerance		
		1P--5P	7P--9P	11P
Dim P	(N-1)×10.0	±0.40	±0.50	±0.60
Dim L	N×10.0+1.8	±0.40	±0.50	±0.60

ANYTEK


CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD


TITLE	NP 10.0mm Series horizontal (C type 后脚靠墙弯) 單數P			DWG NO.	8NP0002	
PART NO.	NPxx11x2xxxxG ⚠					
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.		Tolerance
		Da cheng 2013.12.28	Da cheng 2013.12.28	UNIT: mm		X. ±0.50
				SCALE: NONE		X.X ±0.30
				SHEET: 01/01	REV.: D	X.XX ±0.10 X° ±1°


SIGN	DATE	DESCRIPTION	APPROVER
1			
2			
3			


THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!



SECTION A-A







PCB LAYOUT
TOP VIEW

Material:

- Item ① Terminal body: Thermoplastic (UL94V-0)
- Item ② Terminal side body: Thermoplastic (UL94V-0)
- Item ③ Terminal cover: Thermoplastic (UL94V-0)
- Item ④ Solder pin(front) : Copper, Tin Plated.
- Item ⑤ Solder pin(back) : Copper, Tin Plated.
- Item ⑥ Spring clamp : Stainless steel

Electrical:	cULus
Voltage rating:	600 V
Current rating(SOL):	30 A
Current rating(STR):	40 A
Wire range:	
Solid wire(AWG):	8-20
Stranded wire(AWG):	4-20
Wire strip length:	18-19mm
Withstanding Voltage:	2.2KV
Operating temperature:	-40°C to +115°C
Soldering temperature:	260°C ±5°C/5 Sec
Safety Approval:	
Critical dimension:	

NP xx 1 1 x 2 xxxx G

- xx: No. OF POLES
  - 02: 2 POLES
  - 04: 4 POLES
  - :
  - 12: 12 POLES
- x: Body Color
  - 0 Black (RAL9005)
  - 2 Red (RAL3001/D)
  - 3 Orange(RAL2011/P)
  - 4 Yellow(RAL1018/A)
  - 5 Green(RAL6018/T)
  - 6 Blue (RAL5015/A)
  - 8 Grey(RAL7004/P)
  - 9 White(RAL1102)
  - C Multiple colors
- xxxx:
  - 0000: "@" Logo (Standard)
  - 000A: "ANYTEK" Mark
  - Any special item by customer requst. please contact sales department.
- G: RoHS compliant (lead<4%) In copper Alloy

N=NUMBER OF POLES

DIM		Tolerance		
		2P--4P	6P--8P	10P-12P
Dim P	(N-1)×10.0	±0.40	±0.50	±0.60
Dim L	N×10.0+1.8	±0.40	±0.50	±0.60

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	NP 10.0mm Series horizontal (C type 后脚靠墙型) 双数P				
PART NO.	NPxx11x2xxxxG			DWG NO.	8NP0007
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.	
		Da cheng 2013.12.28	Da cheng 2013.12.28	SHEET: 01/01	UNIT: mm / SCALE: NONE / REV.: B

Tolerance	
X.	±0.50
X.X	±0.30
X.XX	±0.10
X°	±1°