

Test Jacks 4 mm System



Type

KUN 30 / KUN 30 Au

4mm Adapter, nickel/ gold plated brass with solder terminal max 2.5mm². Flexible, shatter-proof insulation sleeve

Pin Diameter

4 mm

PART NO. / Housing color

Nickel Plated

● 931804100

● 931804101

● 931804102

● 931804103

● 931804104

○ 931804107

nickel

Gold Plated

● 931804700

● 931804701

● 931804702

● 931804703

● 931804704

○ 931804707

gold



PB 4

4mm test jack, dimensions according to DIN41649. Suitable for testing PCB boards during operation.

4 mm

● 973582100

● 973582101

Technical Data

Contact Type	jack Ø 4 mm
Connection Type	solder terminal (max. 2.5mm ²)
Voltage Rating	30 VAC / 60 VDC
Measurement Category (IEC61010)	CAT I
Current Rating*	16 A
Contact Resistance	3 mOhm
Mounting Type	–

Material Specifications

Jack Body	nickel plated brass gold plated brass
Contact Spring	–
Housing	PVC-P

Environmental Conditions

Temperature Range	-25°C to +70 °C (-13 to 158°F)
-------------------	--------------------------------

Flamability Rating

Housing	–
---------	---

jack Ø 4 mm

solder
30 VAC / 60 VDC
CAT I
16 A
5 mOhm
PCB

tin plated brass

–



PC

-25°C to +70 °C (-13 to 158°F)

UL 94 HB

Drawing

Measurements are shown in millimeters.
Multiply by 0.03937 to convert to inches.



* Please consider derating graph on page 80.