

承認書

SPECIFICATION FOR APPROVAL

客戶名稱
CUSTOMER

客戶料號
CUS. P/N

尺寸
DIMENSION




CT2-6x6x4

編號
SERIAL NO.

NO. CF1026132255

日期
DATE

2023年6月12日

出圖 DRAWING		
發行 ISSUE	復核 CHECKED	核準 APPROVAL
		
DATE: 2023/6/12		

承認 CUSTOMER APPROVAL



东莞市灿峰电子有限公司

DONG GUAN CITY CAN FENG ELETRONICS CO., LTD

网址: www.canfengele.com E-mail: canfengdianzi@163.com


联系方式

王小姐: 13556646144

洪先生: 13809826886






承認書

SPECIFICATION FOR APPROVAL

規格 ITEM	CT2-6x6x4	編號 SERIAL NO.	NO. CF1026132255
1. 形狀尺寸 (單位mm) ; SHAPE & DIMENSION(unit/mm);		A	6.00 ± 0.5 mm
		B	6.00 ± 0.5 mm
		C	4.00 ± 0.5 mm
		D	
		E	
		F	
		G	
		2. 電器性能檢測項目 ELECTTRONICAL REQUIREMENTS;	
<input type="checkbox"/> L		TEST FREQ	測試儀器 TESTING INSTRUMENTS
<input type="checkbox"/> Q		TEST FREQ	KHZ MHZ 1. Q-METER: <input type="checkbox"/> HP-4342A <input type="checkbox"/> MQ-172
<input checked="" type="checkbox"/> Z	Z1=20 Ω MIN KHZ 25MHZ	Z3=	KHZ MHZ 2. LCR-METER: <input type="checkbox"/> TH2826
	Z2=40 Ω MIN KHZ 100MHZ	Z4=	KHZ MHZ 3. IMPEDANCE ANALYZER: <input checked="" type="checkbox"/> HP-4191A <input type="checkbox"/> Agilent 16092A <input type="checkbox"/> E4991A
溫度 TEMP	25±5℃	濕度 HUMIDITY	60±8% 4. L-METER: <input type="checkbox"/> TH-2775B
繞線: WINDING	Z: Φ 0.5*100L(mm)*0.5TS		5. DIGITAL MINI-OHM METER: VP2941A
3. 外觀 THE LIMIT OF BREAKAGE:			
項目 Item		標準值 Standard Value	
一處缺陷的面积 Area of a breakage		≤1mm ²	
总缺陷面积 ALL area of the breakage		≤2mm ²	
缺陷深度 The depth of the breakge		≤0.4mm	
毛刺长度 The length of burr		≤0.2mm	
4. 包裝 PACKAGING:			
內包裝采用泡塑盒, 外包裝采用紙箱, 每箱產品外面都蓋上标签 (包括品名、數量、批號、檢驗員)。 Inner packing gdopts foam plastics box, outer packing adopts carton and each carton should have a qualified label outside(include the variey, quantity, batch number and inspector).			

檢 測 數 據

INSPECTION DATA

規 格 ITEM	CT2-6x6x4					編 號 SERIAL NO.	NO. CF1026132255							
1. 形壯尺寸(单位/毫米): SHAPE & DIMENSION(unit/mm): =							<input type="checkbox"/> L							
							<input type="checkbox"/> Q				KHZ MHZ			
							<input checked="" type="checkbox"/> Z		Z1=20 Ω MIN KHZ 25MHZ		Z1= KHZ MHZ			
									Z2=40 Ω MIN KHZ 100MHZ		Z4= KHZ MHZ			
							溫 度 TEMP		25±5°C		濕 度 HUMIDITY		60±8%	
							繞 線: WINDING		Z: Φ 0.5*100L(mm)*0.5TS					
項 目 ITEM	电 气 性 能 ELECTRONIC CHARACTERISTICS						尺 寸 DIMENSION(unit:mm)							
	Q	L(μH)	Z1(Ω)	Z2(Ω)	Z3(Ω)	Z4(Ω)	A	B	C	D	E	F		
			20	40			6	6	4					
+			/	/			0.5	0.5	0.5					
-			0	0			0.5	0.5	0.5					
1			30.6	61.2			5.99	6.02	4.01					
2			30.3	59.6			5.98	6.01	4.01					
3			30.8	61.4			6.01	6.02	4.00					
4			30.4	63.1			5.99	6.08	4.02					
5			31.0	64.4			5.98	6.00	4.00					
6			30.6	67.5			6.02	6.08	3.99					
7			30.2	61.8			6.01	6.01	4.02					
8			31.3	60.9			6.02	6.03	4.02					
9			31.2	62.2			6.01	6.04	4.00					
10			31.2	61.4			6.01	6.07	4.00					
X			30.8	62.4			6.00	6.04	4.01					
Y/N			Y	Y			Y	Y	Y					
2. 測試儀器 TESTING INSTRUMENTS HP4191A							檢 測 INSPECTION		復 核 CHECK		確 認 APPROVAL			
														


阻抗 - 頻率曲綫

IMPEDANCE V.S.FREQUENCY (Z-Y)

規格 ITEM	CT2-6x6x4	編號 SERIAL NO.	NO. CF1026132255
------------	-----------	------------------	------------------

材质特性：
MATERIAL CHARACTERISTICS

材料 牌号 Material	初始磁 导率 Initial Permeability	比损耗因子 Relative Loss Factor	比温度系数 Relative Temperature Coefficient	饱和磁通密度 Saturation Magnetic Flux Density	剩磁 Reman- ence	矫顽力 Coercivi- ty	居里温度 Curie Tempera- ture	电阻率 Electric Resistiv- ity	使用范围 Applied Frequency Range	密度 Densit- y
Unit symbol	μ_i $\pm 20\%$	$\tan \delta / \mu_i$ $\times 10^{-6}$	$\alpha \mu_i \gamma$ $\times 10^{-6}$	Bs (MT)	Br (MT)	HC (A/m)	Tc (°C)	ρ ($\Omega \cdot m$)	F Mhz	d g/cm ³
F2	650	20(0.1MHz)	2-5	260(1600A/m)	150	35	>140	>10 ⁵	0.1-1.5	4.6



测试条件； TESTING CONDITION;	檢 測 INSPECTION	復 核 CHECK	确 認 APPROVAL
1. 测试仪器： HP4191A Testing Equipment:			
2. 测试频率区间： 1MHZ-1000MHZ Testing Frequency Range:			
3. 测试绕组： Φ0.5*100L(mm)*0.5TS Testing Coil Specification:			