# T1440101221-000 ✔ ACTIVE


HDC | HDC IP65

TE Internal #: T1440101221-000

Heavy Duty Connector Base Housing, Side Entry, Locking Clip, Sealable, HDC IP65

View on TE.com >

Connectors > Rectangular Connectors > Rectangular Connector Hoods & Bases



Hood & Base Connector Product Type: **Base Housing**

Cable Entry Location: **Side**

Hood & Base Locking Device Type: **Locking Clip**

Sealable: **Yes**

EU RoHS Compliance: **Compliant**

## Features

### Usage Conditions

| | |
|---|---|
| Corrosion Protected | Yes |

### Housing Features

| | |
|---|---|
| Housing Material | Die Cast Aluminum |

### Operation/Application

| | |
|---|---|
| Circuit Application | Power & Signal |

### Mechanical Attachment

| | |
|---|---|
| Thread Size | 2PG21 |
| Hood & Base Locking Device Type | Locking Clip |

### Product Type Features

| | |
|---|---|
| Hood & Base Connector Product Type | Base Housing |
| Sealable | Yes |

### Body Features

| | |
|---|---|
| Cable Entry Location | Side |

### Other

| | |
|---|---|
| EU RoHS Compliance | Compliant |
| EU ELV Compliance | Compliant |

## Product Compliance


For compliance documentation, visit the product page on TE.com>

| | |
|---|---|
| EU RoHS Directive 2011/65/EU | Compliant |
| EU ELV Directive 2000/53/EC | Compliant |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold |
| EU REACH Regulation (EC) No. 1907/2006 | Current ECHA Candidate List: JUNE 2024 (241)<br>Candidate List Declared Against: JUNE 2024 (241)<br>Does not contain REACH SVHC |
| Halogen Content | Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free |
| Solder Process Capability | Not reviewed for solder process capability |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

## Compatible Parts



TE Part # T1210100121-000
H10B-TS-PG21



TE Part # T3609210101-000
DLX-21-MS



TE Part # T1010102100-000
H10B-KDBP



TE Part # T2040102201-000
HE-010-F

## Also in the Series | HDC IP65



Rectangular Connector Hoods & Bases (1257)

## Customers Also Bought



TE Part #T2020082201-000
HD-008-F



TE Part #1-480711-9
15P UMNL CAP HSG BLK



TE Part #T2106062201-000
HWK6/6-012-F



TE Part #640250-1
01P SL156 HSG W/LCK RAMP NATL



TE Part #T0931003003-000
CODING-PIN-M3



TE Part #1SNA195638R2300
M4/6.4A.P




TE Part #T1730060000-000
H6B-TBF-T



TE Part #T2120100219-000
ZGG-10DSTK,1-7,2-8,3-9,4-6,5-10



TE Part #T2120100220-000
ZGGP-H10BSK 1-7/2-8/3-9/4-6/5-10



TE Part #1473203-1
025 CAP ASSY 16P P/BACK BRCKT

## Documents

### Product Drawings

H10B-SGRS-2PG21

English

### CAD Files

3D PDF

3D

### Customer View Model

ENG_CVM_CVM_T1440101221-000_A.2d_dxf.zip

English

### Customer View Model

ENG_CVM_CVM_T1440101221-000_A.3d_igs.zip

English

### Customer View Model

ENG_CVM_CVM_T1440101221-000_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the **Terms and Conditions** of use.

## Datasheets & Catalog Pages

### Heavy Duty Connectors

English

### HEAVY DUTY CONNECTORS

English

### HEAVY DUTY CONNECTORS

Japanese

## Product Specifications

### Application Specification

English