35787 ✔ ACTIVE

PIDG

TE Internal #: 35787

Closed Ring Tongue Terminal, 12 – 10 AWG, #8 / M4 Stud, 4.34 mm [.171 in] Stud Diameter, Closed Barrel, Straight, Tin Plating, PIDG

View on TE.com >

Terminals & Splices > Ring Terminals > PIDG Ring Tongue Terminals







Ring Terminal Product Type: **Closed Ring Tongue Terminal**

Wire Size: **5180 – 13100 CMA**

Stud Size: **#8, M4**

All PIDG Ring Tongue Terminals (410)

Features

Configuration Features

Number of Holes	1

Body Features

Product Weight	2.369 g

Mechanical Attachment

Wire Insulation Support	With

Electrical Characteristics

Voltage Rating	300 V

Industry Standards

Government Qualified Terminal	No

Packaging Features

Packaging Quantity	500
Packaging Method	Loose Piece

Product Type Features

Ring Terminal Product Type	Closed Ring Tongue Terminal
Stud Size	#8, M4
Sealable	No
Wire Insulation Support Retention Type	Insulation Support

Contact Features

Barrel Type	Closed
Terminal Orientation	Straight
Terminal Plating Material	Tin

Dimensions

Wire Size	5180 – 13100 CMA
Stud Diameter	4.34 mm[.171 in]
Tongue Thickness	1.07 mm[.042 in]
Product Length	26.19 mm[1.03 in]
Compatible Insulation Diameter (Max)	5.84 mm[.23 in]
Compatible Insulation Diameter Range	3.81 – 5.84 mm[.15 – .23 in]

Usage Conditions

Insulation Option	Partially Insulated

Operation/Application

Compatible With Wire Base Material	Copper
Compatible With Wire Plating Material	Tin

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC

Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach


Compatible Parts




TE Part # 58423-1
DIE, RBY IS9252



TE Part # 58433-3
PRO CR ASSY, RBY IS9252



TE Part # 679300-1
1210 PIDG CRIMP HEAD



TE Part # 47808-6
DIES PIDG 12-10 DIE SET




TE Part # 169400
CERTI-LOK FRAME W/O DIES



TE Part # 539691-2
ERGO DIE R.B.Y



TE Part # 169404
CERTI-LOK DIE



TE Part # 2063030-1
SDE DIESET, RBY, UL



TE Part # 2217330-2
KIT, BTLI, 4 TON, EU



TE Part # 59239-4
HHHT PIDG PG 12-10 ASSY




TE Part # 59824-1
TETRA-CRIMP PIDG PG FASTON 22-10 ASSY


Also in the Series | PIDG



Compression Connectors(17)



Crimp Wire Pins, Tabs & Ferrules(41)




Knife Disconnects(11)



Quick Disconnects(38)



Ring Terminals(588)



Spade Terminals(228)



Special Purpose Terminals(1)




Splices(41)


Customers Also Bought



TE Part #4-644042-0
10P MTA100 CONN ASSYLF



TE Part #61300-1
SPLICE IS 10000-16000 .031 TPST




TE Part #6-2213766-5
AV19 DPL 3A POWER LED RED 12V



TE Part #320306
TERMINAL,PIDG HK 16-14 8



TE Part #5677792003
RNF-3000-9/3-6-STK



TE Part #41996
SPLICE 7400-10000 CMA TPBR



TE Part #TRAB4103P
OMNI,PH,PMT,410-430MHz

TE Part #20000419-00
TX D558

TE Part #20000420-00
TX D610

TE Part #20000421-00
TX D683

Documents

Product Drawings

TERMINAL,PIDG R 12-10 8

English

CAD Files

Customer View Model

ENG_CVM_CVM_35787_J.2d_dxf.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_35787_J.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_35787_J.3d_stp.zip

English

By downloading the CAD file I accept and agree to the **Terms and Conditions** of use.

Datasheets & Catalog Pages

PIDG TERMINALS & SPLICES Quick Reference Guide

English

Instruction Sheets

Instruction Sheet (U.S.)

English

Agency Approvals

UL Report

English