





1

2

3

4



### Technical requirements:

- 1、 Unit: mm
- 2、 Line diameter: 0.4
- 3、 Material: carbon steel with nicked plated-meet ROHS
- 4、 Style: straight cylinder inside around the center(U)
- 5、 Technics: high temperature of the 260°C heat treatment
- 6、 No be marked sizes is  $\pm 0.25\text{mm}$  tolerances
- 7、 No dirty surface, no bad material
- 8、 Contact number: 13459252012、 0592-5216722
- 9、 Mode: F6-18-0.4-1.2NZU
- 10、 Salt spray test:  
five precent salt spray test was met for 24hours
- 11、 Packaging method: in bags-the minimum package is 2000pcs

						碳钢线			厦门市芯网电子科技有限公司	
标记	处数	分区	更改文件号	签名	年月日	阶段标记	重量	比例		
设计						s		3:1		
校核										
批准										

1

2

3

4