



General Information

| | |
|-------------|---|
| Series | B45192R |
| Dielectric | MnO ₂ Tantalum |
| Style | SMD Chip |
| Description | SMD, Molded, Low Profile, Low ESR, Surge Robust |
| Features | Low Profile, Low ESR, Surge Robust |
| RoHS | Yes |
| Termination | Tin |
| AEC-Q200 | No |
| Notes | Obsolete. Old Part Number [Obsolete] Was B45192R2107M406. |

Specifications

| | |
|-----------------------|--|
| Capacitance | 100 uF |
| Capacitance Tolerance | 20% |
| Voltage DC | 10 VDC (85C), 6.7 VDC (125C) |
| Temperature Range | -55/+125°C |
| Rated Temperature | 85°C |
| Dissipation Factor | 8% |
| Failure Rate | N/A |
| Resistance | 0.2 Ohms (100kHz) |
| Ripple Current | 740 mAmps (25C), 666 mAmps (85C), 296 mAmps (125C) |
| Leakage Current | 10 uA |

Dimensions

| | |
|-----------|----------------|
| Footprint | 7343 |
| L | 7.3mm +/-0.3mm |
| W | 4.3mm +/-0.3mm |
| H | 1.5mm MAX |
| S | 1.3mm +/-0.3mm |
| F | 2.4mm +/-0.1mm |
| K | 1.3mm TYP |

Packaging Specifications

| | |
|--------------------|------------|
| Packaging | T&R, 330mm |
| Packaging Quantity | 4750 |