

CMOS Digital Integrated Circuits Silicon Monolithic

Features

High speed: $t_{pd} = 15 \text{ ns}$ (typ.) at $V_{CC} = 5 \text{ V}$


Low power dissipation: $I_{CC} = 4.0 \mu\text{A}$ (max) at $T_a = 25$

Balanced propagation delays: $t_{PLH} \approx t_{PHL}$

Wide operating voltage range: $V_{CC(opr)} = 2.0$ to 6.0 V

Functional Description

8-Channel Multiplexer



Ordering Information

DEVICE	Package Type	MARKING	Packing	Packing Qty
74HC151N	DIP-16	74HC151	TUBE	1000pcs/box
74HC151M/TR	SOP-16	74HC151	REEL	2500pcs/reel
74HC151MT/TR	TSSOP-16	HC151	REEL	2500pcs/reel

General Description

The 74HC151 is a high speed CMOS 8-CHANNEL MULTIPLEXER fabricated with silicon gate C2MOS technology.


It achieves the high speed operation similar to equivalent LSTTL while maintaining the CMOS low power dissipation.

One of eight data input signals (D0-D7) is selected by decoding of the three-bit address input (A, B, C). The selected data appears on two outputs: non-inverting (Y) and inverting (W).

The strobe input provides two output conditions; a low level on the strobe input transfers the selected data to the outputs. A high level on the strobe input sets the Y output low and the W output high without regard to the data or select input conditions.


All inputs are equipped with protection circuits against static discharge or transient excess voltage.

Pin Assignment



DIP-16/SOP-16/TSSOP-16

IEC Logic Symbol




Truth Table

Inputs				Outputs	
Select			Strobe	Y	W
C	B	A	ST		
X	X	X	H	L	H
L	L	L	L	D0	$\bar{D}0$
L	L	H	L	D1	$\bar{D}1$
L	H	L	L	D2	$\bar{D}2$
L	H	H	L	D3	$\bar{D}3$
H	L	L	L	D4	$\bar{D}4$
H	L	H	L	D5	$\bar{D}5$
H	H	L	L	D6	$\bar{D}6$
H	H	H	L	D7	$\bar{D}7$

X: Don't care

System Diagram



Absolute Maximum Ratings (Note)

Characteristics	Symbol	Note	Rating	Unit
Supply voltage	V_{CC}		-0.5 to 7.0	V
Input voltage	V_{IN}		-0.5 to $V_{CC} + 0.5$	V
Output voltage	V_{OUT}		-0.5 to $V_{CC} + 0.5$	V
Input diode current	I_{IK}		20	mA
Output diode current	I_{OK}		20	mA
Output current	I_{OUT}		25	mA
VCC/ground current	I_{CC}		50	mA
Power dissipation	P_D	(Note 1)	500	mW
Storage temperature	T_{stg}		-65 to 150	°C
Soldering temperature	T_L		260	°C

Note: Exceeding any of the absolute maximum ratings, even briefly, lead to deterioration in IC performance or even destruction.

Using continuously under heavy loads (e.g. the application of high temperature/current/voltage and the significant change in temperature, etc.) may cause this product to decrease in the reliability significantly even if the operating conditions (i.e. operating temperature/current/voltage, etc.) are within the absolute maximum ratings and the operating ranges.

Note 1: P_D derates linearly with -8 mW/ °C above 85

Operating Ranges (Note)

Characteristics	Symbol	Test Condition	Rating	Unit
Supply voltage	V_{CC}		2.0 to 6.0	V
Input voltage	V_{IN}		0 to V_{CC}	V
Output voltage	V_{OUT}		0 to V_{CC}	V
Operating temperature	T_{opr}		-40 to 85	°C
Input rise and fall times	t_r, t_f		0 to 50	µs

Note: The operating ranges must be maintained to ensure the normal operation of the device.

Unused inputs must be tied to either VCC or GND.

Electrical Characteristics

DC Characteristics (Unless otherwise specified, Ta = 25°C)

Characteristics	Symbol	Test Condition		V _{CC} (V)	Min	Typ.	Max	Unit
High-level input voltage	V _{IH}			2.0	1.50			V
				4.5	3.15			
				6.0	4.20			
Low-level input voltage	V _{IL}			2.0			0.50	V
				4.5			1.35	
				6.0			1.80	
High-level output voltage	V _{OH}	V _{IN} = V _{IH} or V _{IL}	I _{OH} = -20μA	2.0	1.9	2.0		V
				4.5	4.4	4.5		
				6.0	5.9	6.0		
			I _{OH} = -4 mA	4.5	4.18	4.31		
			I _{OH} = -5.2 mA	6.0	5.68	5.80		
Low-level output voltage	V _{OL}	V _{IN} = V _{IH} or V _{IL}	I _{OL} = 20μA	2.0		0.0	0.1	V
				4.5		0.0	0.1	
				6.0		0.0	0.1	
			I _{OL} = 4 mA	4.5		0.17	0.26	
			I _{OL} = 5.2 mA	6.0		0.18	0.26	
Input leakage current	I _{IN}	V _{IN} = V _{CC} or GND		6.0			±0.1	μA
Quiescent supply current	I _{CC}	V _{IN} = V _{CC} or GND		6.0			4.0	μA

DC Characteristics (Unless otherwise specified, Ta = -40 to 85°C)

Characteristics	Symbol	Test Condition		V _{CC} (V)	Min	Max	Unit
High-level input voltage	V _{IH}			2.0	1.50		V
				4.5	3.15		
				6.0	4.20		
Low-level input voltage	V _{IL}			2.0		0.50	V
				4.5		1.35	
				6.0		1.80	
High-level output voltage	V _{OH}	V _{IN} = V _{IH} or V _{IL}	I _{OH} = -20μA	2.0	1.9		V
				4.5	4.4		
				6.0	5.9		
			I _{OH} = -4 mA	4.5	4.13		
			I _{OH} = -5.2 mA	6.0	5.63		
Low-level output voltage	V _{OL}	V _{IN} = V _{IH} or V _{IL}	I _{OL} = 20μA	2.0		0.1	V
				4.5		0.1	
				6.0		0.1	
			I _{OL} = 4 mA	4.5		0.33	
			I _{OL} = 5.2 mA	6.0		0.33	
Input leakage current	I _{IN}	V _{IN} = V _{CC} or GND		6.0		±1.0	μA
Quiescent supply current	I _{CC}	V _{IN} = V _{CC} or GND		6.0		40.0	μA

AC Characteristics

(Unless otherwise specified, $C_L = 15 \text{ pF}$, $V_{CC} = 5 \text{ V}$, $T_a = 25^\circ\text{C}$, Input: $t_r = t_f = 6 \text{ ns}$)

Characteristics	Symbol	Test Condition	Min	Typ.	Max	Unit
Output transition time	t_{TLH}, t_{THL}			4	8	ns
Propagation delay time (D-Y)	t_{PLH}, t_{PHL}			15	24	ns
Propagation delay time (D-W)	t_{PLH}, t_{PHL}			15	24	ns
Propagation delay time (ST-Y)	t_{PLH}, t_{PHL}			10	17	ns
Propagation delay time (ST-W)	t_{PLH}, t_{PHL}			10	17	ns
Propagation delay time (A, B, C-Y)	t_{PLH}, t_{PHL}			19	31	ns
Propagation delay time (A, B, C-W)	t_{PLH}, t_{PHL}			19	31	ns

AC Characteristics

(Unless otherwise specified, $C_L = 50 \text{ pF}$, $T_a = 25^\circ\text{C}$, Input: $t_r = t_f = 6 \text{ ns}$)

Characteristics	Symbol	Note	$V_{CC} \text{ (V)}$	Min	Typ.	Max	Unit
Output transition time	t_{TLH}, t_{THL}		2.0		30	75	ns
			4.5		8	15	
			6.0		7	13	
Propagation delay time (D-Y)	t_{PLH}, t_{PHL}		2.0		65	140	ns
			4.5		18	28	
			6.0		15	24	
Propagation delay time (D-W)	t_{PLH}, t_{PHL}		2.0		65	140	ns
			4.5		18	28	
			6.0		15	24	
Propagation delay time (ST-Y)	t_{PLH}, t_{PHL}		2.0		36	100	ns
			4.5		12	20	
			6.0		10	17	
Propagation delay time (ST-W)	t_{PLH}, t_{PHL}		2.0		36	100	ns
			4.5		12	20	
			6.0		10	17	
Propagation delay time (A, B, C-Y)	t_{PLH}, t_{PHL}		2.0		80	180	ns
			4.5		23	36	
			6.0		19	31	
Propagation delay time (A, B, C-W)	t_{PLH}, t_{PHL}		2.0		80	180	ns
			4.5		23	36	
			6.0		19	31	
Input capacitance	C_{IN}				3		pF
Power dissipation capacitance	C_{PD}	(Note 1)			15		pF

Note 1: C_{PD} is defined as the value of the internal equivalent capacitance which is calculated from the operating current consumption without load. Average operating current can be obtained by the equation.

$$I_{CC(opr)} = C_{PD} \times V_{CC} \times f_{IN} + I_{CC}$$


AC Characteristics

(Unless otherwise specified, $C_L = 50 \text{ pF}$, $T_A = -40 \text{ to } 85^\circ\text{C}$, Input: $t_r = t_f = 6 \text{ ns}$)

Characteristics	Symbol	$V_{CC} \text{ (V)}$	Min	Max	Unit
Output transition time	t_{TLH}, t_{THL}	2.0		95	ns
		4.5		19	
		6.0		16	
Propagation delay time (D-Y)	t_{PLH}, t_{PHL}	2.0		175	ns
		4.5		35	
		6.0		30	
Propagation delay time (D-W)	t_{PLH}, t_{PHL}	2.0		175	ns
		4.5		35	
		6.0		30	
Propagation delay time (ST-Y)	t_{PLH}, t_{PHL}	2.0		125	ns
		4.5		25	
		6.0		21	
Propagation delay time (ST-W)	t_{PLH}, t_{PHL}	2.0		125	ns
		4.5		25	
		6.0		21	
Propagation delay time (A, B, C-Y)	t_{PLH}, t_{PHL}	2.0		225	ns
		4.5		45	
		6.0		38	
Propagation delay time (A, B, C-W)	t_{PLH}, t_{PHL}	2.0		225	ns
		4.5		45	
		6.0		38	


Physical Dimensions

DIP-16



Dimensions In Millimeters(DIP-16)											
Symbol:	A	B	D	D1	E	L	L1	a	b	c	d
Min:	6.10	18.94	8.10	7.42	3.10	0.50	3.00	1.50	0.85	0.40	2.54 BSC
Max:	6.68	19.56	10.9	7.82	3.55	0.70	3.60	1.55	0.90	0.50	


SOP-16



Dimensions In Millimeters(SOP-16)									
Symbol:	A	A1	B	C	C1	D	Q	a	b
Min:	1.35	0.05	9.80	5.80	3.80	0.40	0°	0.35	1.27 BSC
Max:	1.55	0.20	10.0	6.20	4.00	0.80	8°	0.45	

Physical Dimensions

TSSOP-16



Dimensions In Millimeters(TSSOP-16)									
Symbol:	A	A1	B	C	C1	D	Q	a	b
Min:	0.85	0.05	4.90	6.20	4.30	0.40	0°	0.20	0.65 BSC
Max:	0.95	0.20	5.10	6.60	4.50	0.80	8°	0.25	

Revision History

REVISION NUMBER	DATE	REVISION	PAGE
V1.0	2014-6	New	1-11
V1.1	2023-7	Update encapsulation type、Update Soldering temperature	1、 4
V1.2	2024-11	Update Lead Temperature	4
V1.3	2025-9	Update important statements、 Update sop-16 Dimension drawing	8、 11

IMPORTANT STATEMENT:

Huaguan Semiconductor reserves the right to change products and services offered without prior notice. Customers should obtain the latest relevant information before placing orders and verify that such information is current and complete. Huaguan Semiconductor assumes no responsibility or liability for altered documents.

Customers are responsible for complying with safety standards and implementing safety measures when using Huaguan Semiconductor products in system design and end-product manufacturing. You assume full responsibility for: selecting the appropriate Huaguan Semiconductor products for your application; designing, validating, and testing your application; and ensuring that your application complies with applicable standards and all other safety, security, or other requirements. This is to prevent potential risks that may lead to personal injury or property damage.

Huaguan Semiconductor products are not approved for use in life support, military, aerospace, or other high-risk applications. Huaguan products are neither intended nor warranted for use in such systems or equipment. Any failure or malfunction may lead to personal injury or severe property damage. Such applications are deemed "Unsafe Use." Unsafe Use includes, but is not limited to: surgical and medical equipment, nuclear energy control equipment, aircraft or spacecraft instruments, control or operation of vehicle power, braking, or safety systems, traffic signal instruments, all types of safety devices, and any other applications intended to support or sustain life. Huaguan Semiconductor shall not be liable for consequences resulting from Unsafe Use in these fields. Users must independently evaluate and assume all risks. Any issues, liabilities, or losses arising from the use of products beyond their approved applications shall be solely borne by the user. Users may not claim any compensation from Huaguan Semiconductor based on these terms. If any third party claims against Huaguan Semiconductor due to such Unsafe Use, the user shall compensate Huaguan Semiconductor for all resulting damages and liabilities.

Huaguan Semiconductor provides technical and reliability data (including datasheets), design resources (including reference designs), application or other design advice, web tools, safety information, and other resources for its semiconductor products. However, no guarantee is made that these resources are free from defects, and no express or implied warranties are provided. The use of testing and other quality control techniques is limited to Huaguan Semiconductor's quality assurance scope. Not all parameters of each device are tested.

Huaguan Semiconductor's documentation authorizes you to use these resources only for developing applications related to the products described herein. You are not granted rights to any other intellectual property of Huaguan Semiconductor or any third party. Any other reproduction or display of these resources is strictly prohibited. You shall fully indemnify Huaguan Semiconductor and its agents against any claims, damages, costs, losses, and liabilities arising from your use of these resources. Huaguan Semiconductor shall not be held responsible.