



REV.	ECN NO OR DESCRIPTION	REVISED	DATE

NOTES:

1. MATERIAL:












- 1). HOUSING MATERIAL: THERMOPLASTIC UL94V-0; COLOR: BLACK
2). CONTACT MATERIAL: BRASS, T=0.60mm

2. FINISH:

- 1). CONTACT FINISH: 50" MIN. NICKEL UNDER PLATED, PLATED 3u" AU ON CONTACT AREA; PLATED COLD FLASH ON SOLDER AREA.
2). FIN DND FINISH: 50u" MIN. NICKEL UNDER PLATED, TIN-PLATED HIGH-TEMPER ATURR 100~160u" IN THE WHOLE SURFACE.

3. ELECTRICAL SPECIFICATIONS:

- 1). VOLTAGE RATING: 12 VAC
2). CURRENT RATING: 2.0A
3). DIELECTRIC STRENGTH: 250V AC FOR MINUTE
4). INSULATION RESISTANCE: 500 MΩ
5). CONTACT RESISTANCE: 50MΩ
6). OPERATION TEMPERATURE: -40° C TO +105° C
7). MAX. PROCESSING TEMP: 260° C FOR 30 SECONDS



UNLESS OTHERWISE
SPECIFIED TOLERANCES

DECIMALS: ANGLES:
X :±0.35 X :±2°
X.X :±0.25 X.X :±1°
X.XX :±0.15



东莞市汉博电子科技有限公司
DONGGUAN HANBO TECHNOLOGY CO., LTD

TITLE	8900 刀片电池座 4.3H			
DWN	xiong	PART NO. BAT-03P43H		
CHKD	lee	SCALE: 1:1	UNIT: mm	
APVD	wang	SIZE: A4	SHEET: 1 OF 1	REV: A4
CUSTOMER COPY				