


## 3-Terminal 0.1A Negative Voltage Regulator

### Description

This series of fixed-voltage monolithic integrated-circuit voltage regulators is designed for a wide range of applications. These applications include on-card regulation for elimination of noise and distribution problems associated with single-point regulation. In addition, they can be used with power-pass elements to make high current voltage regulators.

Each of these regulators can deliver up to 100mA of output current. The internal limiting and thermal shutdown features of these regulators make them essentially immune to overload. When used as a replacement for a zener diode-resistor combination, an effective improvement in output impedance can be obtained together with lower-bias current.



### Features

- Output Current Up to 100mA
- No External Components
- Internal Thermal Overload Protection
- Internal Short-Circuit Limiting
- Output Voltage of -5V, -6V, -8V, -9V, -12V, -15V, -18V and -24V.
- Moisture Sensitivity Level 3

### Ordering Information

DEVICE	Package Type	MARKING	Packing	Packing Qty
LM79L05ACZ/HG	TO-92	79L05A	BAG	1000pcs/box
LM79L06ACZ/HG	TO-92	79L06A	BAG	1000pcs/box
LM79L08ACZ/HG	TO-92	79L08A	BAG	1000pcs/box
LM79L09ACZ/HG	TO-92	79L09A	BAG	1000pcs/box
LM79L12ACZ/HG	TO-92	79L12A	BAG	1000pcs/box
LM79L15ACZ/HG	TO-92	79L15A	BAG	1000pcs/box
LM79L18ACZ/HG	TO-92	79L18A	BAG	1000pcs/box
LM79L24ACZ/HG	TO-92	79L24A	BAG	1000pcs/box
LM79L05ACMK/TR-HG	SOT-89-3	79L05A	REEL	1000pcs/reel
LM79L06ACMK/TR-HG	SOT-89-3	79L06A	REEL	1000pcs/reel
LM79L08ACMK/TR-HG	SOT-89-3	79L08A	REEL	1000pcs/reel
LM79L09ACMK/TR-HG	SOT-89-3	79L09A	REEL	1000pcs/reel
LM79L12ACMK/TR-HG	SOT-89-3	79L12A	REEL	1000pcs/reel
LM79L15ACMK/TR-HG	SOT-89-3	79L15A	REEL	1000pcs/reel
LM79L18ACMK/TR-HG	SOT-89-3	79L18A	REEL	1000pcs/reel
LM79L24ACMK/TR-HG	SOT-89-3	79L24A	REEL	1000pcs/reel

## Absolute Maximum Ratings



CHARACTERISTIC		SYMBOL	MIN.	MAX.	UNIT
Input Voltage	LM79L05A ~ LM79L09A	VIN	-	-30	V
	LM79L12A ~ LM79L18A		-	-35	
	LM79L24		-	-40	
Maximum Power Dissipation at T <sub>A</sub> = 25°C / TO-92		PDMax	-	0.770	W
Thermal Resistance Junction-To-Ambient / TO-92		θJA	-	162	°C/W
Lead Temperature (Soldering, 10 sec)		TSOL	-	260	°C
Storage Temperature Range		TSTG	-65	150	°C
Operating Junction Temperature Range		TJOPR	0	150	°C

**Note:** Absolute Maximum Ratings indicate limits beyond which damage to the device may occur. Operating Ratings indicate conditions for which the device is intended to be functional, but specific performance is not ensured.

## Recommended Operating Conditions

CHARACTERISTIC		SYMBOL	MIN.	MAX.	UNIT
Input Voltage	LM79L05A	VIN	-7	-20	V
	LM79L06A		-8	-20	
	LM79L08A		-10.5	-23	
	LM79L09A		-11.5	-24	
	LM79L12A		-14.5	-27	
	LM79L15A		-17.5	-30	
	LM79L18A		-20.5	-33	
	LM79L24A		-27	-38	
Output Current		I <sub>o</sub>	-	100	mA
Operating Virtual Junction Temperature		T <sub>J</sub>	0	125	°C


## Pin Configuration



## Pin Description

Pin No.	TO-92 / SOT89-3 LEAD	
	Name	Function
1	GND	Ground
2	VIN	Input Voltage
3	VOUT	Output Voltage

## Typical Application



Note 1. To specify an output voltage, substitute voltage for "XX".

Note 2. Bypass capacitors are recommended for optimum stability and transient response and should be located as close as possible to the regulators.

## Electrical Characteristics

### LM79L05A (At specified virtual junction temperature, $V_{IN} = -10V$ , $I_o = 40mA$ (Unless otherwise noted))

PARAMETER	SYMBOL	TEST CONDITION <sup>(Note 1)</sup>		MIN.	TYP.	MAX.	UNIT
Output Voltage <sup>(Note 2)</sup>	V <sub>OUT</sub>		25°C	-4.8	-5	-5.2	V
		1mA ≤ I <sub>o</sub> ≤ 40mA -7V ≤ V <sub>IN</sub> ≤ 20V	0°C ~125°C	-4.75	-5	-5.25	
		1mA ≤ I <sub>o</sub> ≤ 70mA		-4.75	-5	-5.25	
Line Regulation	ΔV <sub>LINE</sub>	-7V ≤ V <sub>IN</sub> ≤ -20V	25°C		32	150	mV
		-8V ≤ V <sub>IN</sub> ≤ -20V			26	100	
Load Regulation	ΔV <sub>LOAD</sub>	1mA ≤ I <sub>o</sub> ≤ 100mA	25°C		15	60	mV
		1mA ≤ I <sub>o</sub> ≤ 40mA			8	30	
Bias Current	I <sub>B</sub>		25°C		3.8	6	mA
			125°C			5.5	
Bias Current Change	ΔI <sub>B</sub>	-8V ≤ V <sub>IN</sub> ≤ -20V	0°C ~125°C			1.5	mA
		1mA ≤ I <sub>o</sub> ≤ 40mA				0.1	
Output Noise Voltage	V <sub>N</sub>	10Hz ≤ f ≤ 100kHz	25°C		42		uV
Ripple Rejection	RR	-8V ≤ V <sub>IN</sub> ≤ -18V, f=120Hz	25°C	41	49		dB
Dropout Voltage	V <sub>D</sub>		25°C		1.7		V

### LM79L06A (At specified virtual junction temperature, $V_{IN} = -11V$ , $I_o = 40mA$ (Unless otherwise noted))

PARAMETER	SYMBOL	TEST CONDITION <sup>(Note 1)</sup>		MIN.	TYP.	MAX.	UNIT
Output Voltage <sup>(Note 2)</sup>	V <sub>OUT</sub>		25°C	-5.76	-6	-6.24	V
		1mA ≤ I <sub>o</sub> ≤ 40mA -8V ≤ V <sub>IN</sub> ≤ -21V	0°C ~125°C	-5.7	-6	-6.3	
		1mA ≤ I <sub>o</sub> ≤ 70mA		-5.7	-6	-6.3	
Line Regulation	ΔV <sub>LINE</sub>	-8V ≤ V <sub>IN</sub> ≤ -21V	25°C		50	150	mV
		-9V ≤ V <sub>IN</sub> ≤ -21V			45	110	
Load Regulation	ΔV <sub>LOAD</sub>	1mA ≤ I <sub>o</sub> ≤ 100mA	25°C		12	70	mV
		1mA ≤ I <sub>o</sub> ≤ 40mA			5.5	35	
Bias Current	I <sub>B</sub>		25°C			6	mA
			125°C			5.5	
Bias Current Change	ΔI <sub>B</sub>	-9V ≤ V <sub>IN</sub> ≤ -21V	0°C ~125°C			1.5	mA
		1mA ≤ I <sub>o</sub> ≤ 40mA				0.1	
Output Noise Voltage	V <sub>N</sub>	10Hz ≤ f ≤ 100kHz	25°C		50		uV
Ripple Rejection	RR	-9V ≤ V <sub>IN</sub> ≤ -19V, f=120Hz	25°C	39	47		dB
Dropout Voltage	V <sub>D</sub>		25°C		1.7		V

**LM79L08A** (At specified virtual junction temperature,  $V_{IN} = -14V$ ,  $I_o = 40mA$  (Unless otherwise noted))

PARAMETER	SYMBOL	TEST CONDITION <sup>(Note 1)</sup>	MIN.	TYP.	MAX.	UNIT	
Output Voltage <sup>(Note 2)</sup>	V <sub>OUT</sub>		25°C	-7.7	-8	-8.3	V
		1mA ≤ I <sub>o</sub> ≤ 40mA -10.5V ≤ V <sub>IN</sub> ≤ -23V	0°C ~125°C	-7.6	-8	-8.4	
		1mA ≤ I <sub>o</sub> ≤ 70mA		-7.6	-8	-8.4	
Line Regulation	ΔV <sub>LINE</sub>	-10.5V ≤ V <sub>IN</sub> ≤ -23V	25°C		20	175	mV
		-11V ≤ V <sub>IN</sub> ≤ -23V			12	125	
Load Regulation	ΔV <sub>LOAD</sub>	1mA ≤ I <sub>o</sub> ≤ 100mA	25°C		18	80	mV
		1mA ≤ I <sub>o</sub> ≤ 40mA			9	42	
Bias Current	I <sub>B</sub>		25°C			6.5	mA
			125°C			6	
Bias Current Change	ΔI <sub>B</sub>	-11V ≤ V <sub>IN</sub> ≤ -23V	0°C ~125°C			1.5	mA
		1mA ≤ I <sub>o</sub> ≤ 40mA				0.1	
Output Noise Voltage	V <sub>N</sub>	10Hz ≤ f ≤ 100kHz	25°C		60	uV	
Ripple Rejection	RR	-12V ≤ V <sub>IN</sub> ≤ -23V, f=120Hz	25°C	42	49	dB	
Dropout Voltage	V <sub>D</sub>		25°C		1.7	V	

**LM79L09A** (At specified virtual junction temperature,  $V_{IN} = -15V$ ,  $I_o = 40mA$  (Unless otherwise noted))

PARAMETER	SYMBOL	TEST CONDITION <sup>(Note 1)</sup>	MIN.	TYP.	MAX.	UNIT	
Output Voltage <sup>(Note 2)</sup>	V <sub>OUT</sub>		25°C	-8.64	-9	-9.36	V
		1mA ≤ I <sub>o</sub> ≤ 40mA -11V ≤ V <sub>IN</sub> ≤ -24V	0°C ~125°C	-8.55	9	-9.45	
		1mA ≤ I <sub>o</sub> ≤ 70mA		-8.55	9	-9.45	
Line Regulation	ΔV <sub>LINE</sub>	-11V ≤ V <sub>IN</sub> ≤ -24V	25°C		80	200	mV
		-12V ≤ V <sub>IN</sub> ≤ -24V			20	160	
Load Regulation	ΔV <sub>LOAD</sub>	1mA ≤ I <sub>o</sub> ≤ 100mA	25°C		17	90	mV
		1mA ≤ I <sub>o</sub> ≤ 40mA			8	45	
Bias Current	I <sub>B</sub>		25°C		3.8	6.5	mA
			125°C			6	
Bias Current Change	ΔI <sub>B</sub>	-12V ≤ V <sub>IN</sub> ≤ -24V	0°C ~125°C			1.5	mA
		1mA ≤ I <sub>o</sub> ≤ 40mA				0.1	
Output Noise Voltage	V <sub>N</sub>	10Hz ≤ f ≤ 100kHz	25°C		64	uV	
Ripple Rejection	RR	-8V ≤ V <sub>IN</sub> ≤ -18V, f=120Hz	25°C	35	43	dB	
Dropout Voltage	V <sub>D</sub>		25°C		1.7	V	

**LM79L12A** (At specified virtual junction temperature,  $V_{IN} = -19V$ ,  $I_o = 40mA$  (Unless otherwise noted))

PARAMETER	SYMBOL	TEST CONDITION <sup>(Note 1)</sup>		MIN.	TYP.	MAX.	UNIT
Output Voltage <sup>(Note 2)</sup>	$V_{OUT}$		25°C	-11.5	-12	-12.5	V
		$1mA \leq I_o \leq 40mA$ $-14.5V \leq V_{IN} \leq -27V$	0°C ~125°C	-11.4	-12	-12.6	
		$1mA \leq I_o \leq 70mA$		-11.4	-12	-12.6	
Line Regulation	$\Delta V_{LINE}$	$-14.5V \leq V_{IN} \leq -27V$	25°C		50	250	mV
		$-16V \leq V_{IN} \leq -27V$			40	200	
Load Regulation	$\Delta V_{LOAD}$	$1mA \leq I_o \leq 100mA$	25°C		24	100	mV
		$1mA \leq I_o \leq 40mA$			15	50	
Bias Current	$I_B$		25°C			6.5	mA
			125°C			6	
Bias Current Change	$\Delta I_B$	$-16V \leq V_{IN} \leq -27V$	0°C ~125°C			1.5	mA
		$1mA \leq I_o \leq 40mA$				0.1	
Output Noise Voltage	$V_N$	10Hz ≤ f ≤ 100kHz	25°C		70		μV
Ripple Rejection	RR	$-15V \leq V_{IN} \leq -25V, f=120Hz$	25°C	37	42		dB
Dropout Voltage	$V_D$		25°C		1.7		V

**LM79L15A** (At specified virtual junction temperature,  $V_{IN} = -23V$ ,  $I_o = 40mA$  (Unless otherwise noted))

PARAMETER	SYMBOL	TEST CONDITION <sup>(Note 1)</sup>		MIN.	TYP.	MAX.	UNIT
Output Voltage <sup>(Note 2)</sup>	$V_{OUT}$		25°C	-14.4	-15	-15.6	V
		$1mA \leq I_o \leq 40mA$ $-17.5V \leq V_{IN} \leq -30V$	0°C ~125°C	-14.25	-15	-15.75	
		$1mA \leq I_o \leq 70mA$		-14.25	-15	-15.75	
Line Regulation	$\Delta V_{LINE}$	$-17.5V \leq V_{IN} \leq -30V$	25°C		65	300	mV
		$-27V \leq V_{IN} \leq -30V$			58	250	
Load Regulation	$\Delta V_{LOAD}$	$1mA \leq I_o \leq 100mA$	25°C		25	150	mV
		$1mA \leq I_o \leq 40mA$			15	75	
Bias Current	$I_B$		25°C		4.2	6.5	mA
			125°C			6	
Bias Current Change	$\Delta I_B$	$-20V \leq V_{IN} \leq -30V$	0°C ~125°C			1.5	mA
		$1mA \leq I_o \leq 40mA$				0.1	
Output Noise Voltage	$V_N$	10Hz ≤ f ≤ 100kHz	25°C		82		μV
Ripple Rejection	RR	$-18.5V \leq V_{IN} \leq -28.5V, f=120Hz$	25°C	37	44		dB
Dropout Voltage	$V_D$		25°C		1.7		V

**LM79L18A** (At specified virtual junction temperature,  $V_{IN} = -26V$ ,  $I_o = 40mA$  (Unless otherwise noted))

PARAMETER	SYMBOL	TEST CONDITION <sup>(Note 1)</sup>		MIN.	TYP.	MAX.	UNIT
Output Voltage <sup>(Note 2)</sup>	$V_{OUT}$		25°C	-17.3	-18	-18.7	V
		$1mA \leq I_o \leq 40mA$ $-20.5V \leq V_{IN} \leq -33V$	0°C ~125°C	-17.1	-18	-18.9	
		$1mA \leq I_o \leq 70mA$		-17.1	-18	-18.9	
Line Regulation	$\Delta V_{LINE}$	$-20.7V \leq V_{IN} \leq -33V$	25°C		70	360	mV
		$-21V \leq V_{IN} \leq -33V$			64	300	
Load Regulation	$\Delta V_{LOAD}$	$1mA \leq I_o \leq 100mA$	25°C		27	180	mV
		$1mA \leq I_o \leq 40mA$			19	90	
Bias Current	$I_B$		25°C		4.7	6.5	mA
			125°C			6	
Bias Current Change	$\Delta I_B$	$-21V \leq V_{IN} \leq -33V$	0°C ~125°C			1.5	mA
		$1mA \leq I_o \leq 40mA$				0.1	
Output Noise Voltage	$V_N$	$10Hz \leq f \leq 100kHz$	25°C		82		uV
Ripple Rejection	RR	$-23V \leq V_{IN} \leq -33V, f=120Hz$	25°C	32	36		dB
Dropout Voltage	$V_D$		25°C		1.7		V

**LM79L24A** (At specified virtual junction temperature,  $V_{IN} = -32V$ ,  $I_o = 40mA$  (Unless otherwise noted))


PARAMETER	SYMBOL	TEST CONDITION <sup>(Note 1)</sup>		MIN.	TYP.	MAX.	UNIT
Output Voltage <sup>(Note 2)</sup>	$V_{OUT}$		25°C	-23	-24	-25	V
		$1mA \leq I_o \leq 40mA$ $-27V \leq V_{IN} \leq -38V$	0°C ~125°C	-22.8	-24	-25.2	
		$1mA \leq I_o \leq 70mA$		-22.8	-24	-25.2	
Line Regulation	$\Delta V_{LINE}$	$-27V \leq V_{IN} \leq -38V$	25°C		95	480	mV
		$-28V \leq V_{IN} \leq -38V$			78	400	
Load Regulation	$\Delta V_{LOAD}$	$1mA \leq I_o \leq 100mA$	25°C		41	240	mV
		$1mA \leq I_o \leq 40mA$			28	120	
Bias Current	$I_B$		25°C		4.8	6.5	mA
			125°C			6	
Bias Current Change	$\Delta I_B$	$-21V \leq V_{IN} \leq -38V$	0°C ~125°C			1.5	mA
		$1mA \leq I_o \leq 40mA$				0.1	
Output Noise Voltage	$V_N$	$10Hz \leq f \leq 100kHz$	25°C		82		uV
Ripple Rejection	RR	$-29V \leq V_{IN} \leq -35V, f=120Hz$	25°C	30	33		dB
Dropout Voltage	$V_D$		25°C		1.7		V

Note 1. Pulse testing techniques are used to maintain the junction temperature as close to the ambient temperature as possible. Thermal effects must be taken into account separately.


All characteristics are measured with a 0.33uF capacitor across the input and a 0.1uF capacitor across the output.

Note 2. This specification applies only for DC power dissipation permitted by absolute maximum ratings.


**Typical Operating Characteristics**




Power Dissipation vs. Ambient Temperature, TO-92




Dropout Voltage vs. Ambient Temperature



Output Voltage vs. Input Voltage




Quiescent Current vs. Input Voltage



Output Voltage vs. Output Current


## Physical Dimensions

TO-92



Dimensions In Millimeters(TO-92)									
Symbol:	A	B	C	C1	D	D1	L	a	b
Min:	3.43	4.44	13.5	4.32	3.17	2.03	0.33	0.40	1.27BSC
Max:	4.13	5.21	15.3	5.34	4.19	2.67	0.42	0.52	

SOT89-3



Dimensions In Millimeters(SOT89-3)									
Symbol:	A	B	C	C1	D	L	a	b	e
Min:	1.40	4.40	3.94	2.30	0.90	0.35	0.40	1.50	1.55
Max:	1.60	4.60	4.25	2.60	1.20	0.44	0.55	BSC	BSC

## Revision History

REVISION NUMBER	DATE	REVISION	PAGE
V1.0	2014-1	New	1-11
V1.1	2019-07	Modify the package dimension diagram SOT-89-3、 Update Package Type	1、 9
V1.2	2024-12	Update Lead Temperature	2
V1.3	2025-12	Update important statements	11

**IMPORTANT STATEMENT:**

Huaguan Semiconductor reserves the right to change products and services offered without prior notice. Customers should obtain the latest relevant information before placing orders and verify that such information is current and complete. Huaguan Semiconductor assumes no responsibility or liability for altered documents.

Customers are responsible for complying with safety standards and implementing safety measures when using Huaguan Semiconductor products in system design and end-product manufacturing. You assume full responsibility for: selecting the appropriate Huaguan Semiconductor products for your application; designing, validating, and testing your application; and ensuring that your application complies with applicable standards and all other safety, security, or other requirements. This is to prevent potential risks that may lead to personal injury or property damage.

Huaguan Semiconductor products are not approved for use in life support, military, aerospace, or other high-risk applications. Huaguan products are neither intended nor warranted for use in such systems or equipment. Any failure or malfunction may lead to personal injury or severe property damage. Such applications are deemed "Unsafe Use." Unsafe Use includes, but is not limited to: surgical and medical equipment, nuclear energy control equipment, aircraft or spacecraft instruments, control or operation of vehicle power, braking, or safety systems, traffic signal instruments, all types of safety devices, and any other applications intended to support or sustain life. Huaguan Semiconductor shall not be liable for consequences resulting from Unsafe Use in these fields. Users must independently evaluate and assume all risks. Any issues, liabilities, or losses arising from the use of products beyond their approved applications shall be solely borne by the user. Users may not claim any compensation from Huaguan Semiconductor based on these terms. If any third party claims against Huaguan Semiconductor due to such Unsafe Use, the user shall compensate Huaguan Semiconductor for all resulting damages and liabilities.

Huaguan Semiconductor provides technical and reliability data (including datasheets), design resources (including reference designs), application or other design advice, web tools, safety information, and other resources for its semiconductor products. However, no guarantee is made that these resources are free from defects, and no express or implied warranties are provided. The use of testing and other quality control techniques is limited to Huaguan Semiconductor's quality assurance scope. Not all parameters of each device are tested.

Huaguan Semiconductor's documentation authorizes you to use these resources only for developing applications related to the products described herein. You are not granted rights to any other intellectual property of Huaguan Semiconductor or any third party. Any other reproduction or display of these resources is strictly prohibited. You shall fully indemnify Huaguan Semiconductor and its agents against any claims, damages, costs, losses, and liabilities arising from your use of these resources. Huaguan Semiconductor shall not be held responsible.