

LOOSE PIECE		SPECIFICATIONS						
MATERIAL NUMBER	ENGINEERING NUMBER	STUD SIZE	"S" ±.005 [0.13]	"W" ±.010 [0.25]	"C" MIN.	"L" MAX.	"H"	STOCK THICKNESS
191300005	A-234-06X	6	.146 [3.71]	.291 [7.39]	.207 [5.26]	.835 [21.21]	---	.028 $\frac{+.001}{-.000}$ [0.71]
191300006	A-234-08X	8	.173 [4.39]					
191300007	A-234-10X	10	.198 [5.03]					
191300008	A-238-04X	4	.119 [3.02]	.245 [6.22]	.207 [5.26]	.835 [21.21]	.980 [24.89]	.028 $\frac{+.001}{-.000}$ [0.71]
191300009	A-238-06X	6	.146 [3.71]					





PARTS ON TAPE

NOTES:

1. MATERIAL:
   (A). SPADE TONGUE TERMINAL: COPPER
   PLATING: ELECTRO-TIN (.0003 MIN.)
   (B). INSULATION: MOLDED PVC (RED)
2. MWID: MAXIMUM WIRE INSULATION DIAMETER
3. WIRE SIZE: 22 -18 AWG
   0.25 -1.5 MM²
4. ALL DIMENSIONS IN INCHES/[MM].
5. PARTS ARE ROHS COMPLIANT.
6. DIMS. SHOWN ARE FOR REFERENCE ONLY.

DOCUMENT STATUS	P1	RELEASE DATE	2023/10/19 12:42:23

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

DIMENSION UNITS	SCALE
INCH/mm	NTS

GENERAL TOLERANCES (UNLESS SPECIFIED)

	MM	INCH
4 PLACES	±	±
3 PLACES	±	± 0.005
2 PLACES	± 0.13	± 0.01
1 PLACE	± 0.25	±
0 PLACES	±	±
ANGULAR TOL	± 0.5 °	

DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS

CURRENT REV DESC: REMOVED OBSOLETED PART NUMBERS AS PER PCN#512600

EC NO: 765006
DRWN: MADHAM5 2023/09/01
CHK'D: GGA 2023/10/19
APPR: GGA 2023/10/19

INITIAL REVISION:
DRWN: JJ 1984/10/29
APPR: JMACNEIL 2019/08/05

THIRD ANGLE PROJECTION | DRAWING: C-SIZE | SERIES: 19130

molex

SPADE TONGUE TERMINAL
INSULKRIMP 200-SERIES

PRODUCT CUSTOMER DRAWING

DOCUMENT NUMBER	DOC TYPE	DOC PART	REVISION
191300004	PSD	000	A1

MATERIAL NUMBER	CUSTOMER	SHEET NUMBER
SEE TABLE	GENERAL MARKET	1 OF 1

FORMAT: Eng-lega-master-B-prod-C
REVISION: E1
DATE: 2021/05/01