

## 1.Features

- $V_{DS(V)} = -30V$
- $I_D = -12A$
- $R_{DS(ON)} < 11.9m\Omega (V_{GS} = -10V)$
- $R_{DS(ON)} < 19.7m\Omega (V_{GS} = -4.5V)$



## 2.Application

- Charge and Discharge Switch for Notebook PC Battery Application

## 3.Pinning information

Pin	Symbol	Description
1,2,3	S	SOURCE
4	G	GATE
5,6,7,8	D	DRAIN

SOP-8



## 4.Absolute Maximum Ratings

Parameter		Symbol	Rating	Units
Drain- Source Voltage		$V_{DS}$	-30	V
Gate-to-Source Voltage		$V_{GS}$	±20	V
Continuous Drain Current, $V_{GS} = 10V$	$T_A = 25^\circ C$	$I_D$	-12	A
Continuous Drain Current, $V_{GS} = 10V$	$T_A = 70^\circ C$		-9.6	A
Pulsed Drain Current ①		$I_{DM}$	-96	A
Power Dissipation ④	$T_A = 25^\circ C$	$P_D$	2.5	W
Power Dissipation ④	$T_A = 70^\circ C$		1.6	W
Linear Derating Factor			0.02	W/°C
Junction and Storage Temperature Range		$T_J, T_{STG}$	-55 to 150	°C



## 5. Electrical Characteristics $T_J = 25^\circ\text{C}$ unless otherwise noted

Parameter	Symbol	Conditions	Min	Typ	Max	Units	
<b>Static</b>							
Drain-Source Breakdown Voltage	$BV_{DSS}$	$I_D = -250\mu\text{A}$ , $V_{GS} = 0\text{V}$	-30			V	
Breakdown Voltage Temp. Coefficient	$\Delta BV_{DSS}/\Delta T_J$	$I_D = -1\text{mA}$ , Reference to $25^\circ\text{C}$		0.021		V/ $^\circ\text{C}$	
Static Drain-to-Source On-Resistance	$R_{DS(ON)}$	$V_{GS} = -10\text{V}$ , $I_D = -12\text{A}$ ③		10	11.9	m $\Omega$	
		$V_{GS} = -4.5\text{V}$ , $I_D = -9.6\text{A}$ ③		16.1	19.7		
Gate Threshold Voltage	$V_{GS(th)}$	$V_{DS} = V_{GS}$ , $I_D = -25\mu\text{A}$	-1	-1.5	-2	V	
Gate Threshold Voltage Coefficient	$\Delta V_{GS(th)}$			-5.8		mV/ $^\circ\text{C}$	
Drain-to-Source Leakage Current	$I_{DSS}$	$V_{DS} = -24\text{V}$ , $V_{GS} = 0\text{V}$			-1	$\mu\text{A}$	
		$V_{DS} = -24\text{V}$ , $V_{GS} = 0\text{V}$ , $T_J = 125^\circ\text{C}$			-150	$\mu\text{A}$	
Gate-to-Source Forward Leakage	$I_{GSS}$	$V_{GS} = -20\text{V}$			-100	nA	
Gate-to-Source Reverse Leakage		$V_{GS} = 20\text{V}$			100	nA	
Forward Transconductance	$g_{FS}$	$V_{DS} = -10\text{V}$ , $I_D = -9.6\text{A}$	20			S	
Total Gate Charge ⑥	$Q_g$	$V_{DS} = -15\text{V}$ , $V_{GS} = -4.5\text{V}$ , $I_D = -9.6\text{A}$		18		nC	
Total Gate Charge ⑥	$Q_g$	$V_{DS} = -10\text{V}$		35	52	nC	
Gate-to-Source Charge ⑥	$Q_{gs}$	$V_{GS} = -15\text{V}$		5.3		nC	
Gate-to-Drain Charge ⑥	$Q_{gd}$	$I_D = -9.6\text{A}$		8.5		nC	
Gate Resistance ⑥	$R_g$			15		$\Omega$	
Turn-On Delay Time	$t_{D(on)}$	$V_{DD} = -15\text{V}$ , $V_{GS} = -4.5\text{V}$ ③		19		ns	
Rise Time	$t_r$		$I_D = -1\text{A}$		57		ns
Turn-Off Delay Time	$t_{D(off)}$		$R_G = 6.8\Omega$		80		ns
Fall Time	$t_f$		See Figs. 20a & 20b		66		ns
Input Capacitance	$C_{iss}$	$V_{GS} = 0\text{V}$		1680		pF	
Output Capacitance	$C_{oss}$	$V_{DS} = -25\text{V}$		350		pF	
Reverse Transfer Capacitance	$C_{rss}$	$f = 1.0\text{MHz}$		220		pF	
<b>Avalanche Characteristics</b>							
Single Pulse Avalanche Energy ②	$E_{AS}$				120	mJ	
Avalanche Current ①	$I_{AR}$				-9.6	A	



Diode Characteristics						
Continuous Source Current (Body Diode)	$I_S$	MOSFET symbol showing the integral reverse p-n junction diode.			-2.5	A
Pulsed Source Current (Body Diode) ①	$I_{SM}$				-96	
Diode Forward Voltage	$V_{SD}$	$T_J=25^\circ\text{C}, I_S=-2.5\text{A}, V_{GS}=0\text{V}$ ③			-1.2	V
Reverse Recovery Time	$t_{rr}$	$T_J=25^\circ\text{C}, I_F=-2.5\text{A}, V_{DD}=-24\text{V}$ $dI/dt=100\text{A}/\mu\text{s}$ ③		51	76	ns
Reverse Recovery Charge	$Q_{rr}$			35	53	nC
Thermal Resistance						
Junction-to-Drain Lead ⑤	$R_{\theta JL}$				20	$^\circ\text{C}/\text{W}$
Junction-to-Ambient ④	$R_{\theta JA}$				50	$^\circ\text{C}/\text{W}$

## Notes:

- ① Repetitive rating; pulse width limited by max. junction temperature.
- ② Starting  $T_J=25^\circ\text{C}$ ,  $L=2.6\text{mH}$ ,  $R_G=25\Omega$ ,  $I_{AS}=-9.6\text{A}$ .
- ③ Pulse width  $\leq 400\mu\text{s}$ ; duty cycle  $\leq 2\%$ .
- ④ When mounted on 1 inch square copper board.
- ⑤  $R_\theta$  is measured at  $T_J$  of approximately  $90^\circ\text{C}$ .
- ⑥ For DESIGN AID ONLY, not subject to production testing.



## 6.1 Typical Characteristics

<p>-I<sub>D</sub> - Drain-to-Source Current (A)</p> <p>-V<sub>DS</sub> - Drain-to-Source Voltage (V)</p>	<p>-I<sub>D</sub> - Drain-to-Source Current (A)</p> <p>-V<sub>DS</sub> - Drain-to-Source Voltage (V)</p>
<p>Fig 1. Typical Output Characteristics</p>	<p>Fig 2. Typical Output Characteristics</p>
<p>-I<sub>D</sub> - Drain-to-Source Current (A)</p> <p>-V<sub>GS</sub>, Gate-to-Source Voltage (V)</p>	<p>R<sub>DS(on)</sub>, Drain-to-Source On Resistance (Normalized)</p> <p>T<sub>J</sub>, Junction Temperature (°C)</p>
<p>Fig 3. Typical Transfer Characteristics</p>	<p>Fig 4. Normalized On-Resistance Vs. Temperature</p>
<p>C, Capacitance (pF)</p> <p>-V<sub>DS</sub>, Drain-to-Source Voltage (V)</p>	<p>-V<sub>GS</sub>, Gate-to-Source Voltage (V)</p> <p>Q<sub>G</sub>, Total Gate Charge (nC)</p>
<p>Fig 5. Typical Capacitance Vs. Drain-to-Source Voltage</p>	<p>Fig 6. Typical Gate Charge Vs. Gate-to-Source Voltage</p>




## 6.2 Typical Characteristics

<p>Fig 7. Typical Source-Drain Diode Forward Voltage</p>	<p>Fig 8. Maximum Safe Operating Area</p>
<p>Fig 9. Maximum Drain Current vs. Ambient Temperature</p>	<p>Fig 10. Threshold Voltage vs. Temperature</p>
<p>Fig 11. On-Resistance vs. Gate Voltage</p>	<p>Fig 12. Typical On-Resistance vs. Drain Current</p>



## 6.3 Typical Characteristics






Fig 16a. Gate Charge Test Circuit




Fig 16b. Gate Charge Waveform




Fig 17a. Unclamped Inductive Test Circuit




Fig 17b. Unclamped Inductive Waveforms




Fig 18a. Switching Time Test Circuit





Fig 18b. Switching Time Waveforms



## 7.SOP-8 Package Outline Dimensions




### DIMENSIONS (mm are the original dimensions)

Symbol	A	A1	A2	A3	b	c	D	E	E1	e	h	L
Min	-	0.05	1.30	0.60	0.39	0.20	4.80	5.80	3.80	1.24	0.30	0.50
Max	1.75	0.20	1.50	0.70	0.47	0.24	5.00	6.20	4.00	1.30	0.50	0.80

Symbol	L1	θ
Min	1.00	0°
Max	1.10	8°



## 8. Ordering information



yy: Year Code  
ww: Week Code

Order Code	Package	Base QTY	Delivery Mode
UMW IRF9328TR	SOP-8	3000	Tape and reel



## 9. Disclaimer

---

UMW reserves the right to make changes to all products, specifications. Customers should obtain the latest version of product documentation and verify the completeness and currency of the information before placing an order.

When applying our products, please do not exceed the maximum rated values, as this may affect the reliability of the entire system. Under certain conditions, any semiconductor product may experience faults or failures. Buyers are responsible for adhering to safety standards and implementing safety measures during system design, prototyping, and manufacturing when using our products to prevent potential failure risks that could lead to personal injury or property damage.

Unless explicitly stated in writing, UMW products are not intended for use in medical, life-saving, or life-sustaining applications, nor for any other applications where product failure could result in personal injury or death. If customers use or sell the product for such applications without explicit authorization, they assume all associated risks.

When reselling, applying, or exporting, please comply with export control laws and regulations of China, the United States, the United Kingdom, the European Union, and other relevant countries, regions, and international organizations.

This document and any actions by UMW do not grant any intellectual property rights, whether express or implied, by estoppel or otherwise. The product names and marks mentioned herein may be trademarks of their respective owners.