
DUAL-IN-LINE SOCKETS

SERIES 110 • SELECTIVELY LOADED RELAY DIP SOCKET, SOLDER TAIL






Fig. 1




Fig. 2




Fig. 3




Fig. 4




Fig. 5





Fig. 6

○ = Loaded Position ● = Empty Position

- Relay sockets accept devices with I/O pins on 2,54 grid
- Additional Relay DIP socket patterns are available on Page 134
- Series 110 use MM #1001 receptacles. See page 165 for details
- Hi-Rel, 4-finger BeCu #30 contact is rated at 3 amps. See page 253 for details
- Insulators are high temperature thermoplastic, suitable for all soldering operations
- For Electrical, Mechanical and Environmental Data, see page 264 for details



ORDERING INFORMATION

FIG. 1	**Series 110...002**	**8 Position Relay Socket**
	110-XX-210-10-002000	
FIG. 2	**Series 110...002**	**8 Position Relay Socket**
	110-XX-314-10-002000	
FIG. 3	**Series 110...003**	**8 Position Relay Socket**
	110-XX-316-10-003000	
FIG. 4	**Series 110...004**	**4 Position Relay Socket**
	110-XX-316-10-004000	
FIG. 5	**Series 110...005**	**8 Position Relay Socket**
	110-XX-316-10-005000	
FIG. 6	**Series 110...002**	**14 Position Relay Socket**
	110-XX-328-10-002000	

XX=Plating Code See Below

RoHS-2 2011/65/EU

SPECIFY PLATING CODE XX=	13 ◆		93			43 ◆	
Sleeve (Pin)	0,25µm Au		5,08µm Sn/Pb			5,08µm Sn	
Contact (Clip)	0,76µm Au		0,76µm Au			0,76µm Au	

Mill-Max Mfg. Corp. • 190 Pine Hollow Road, P.O. Box 300, Oyster Bay, NY 11771 • 516-922-6000 • Fax: 516-922-9253 • www.mill-max.com