



MAT'L NO (LOOSE PC)	ENG NO (LOOSE PC)	MAT'L NO (ON TAPE)	ENG NO (ON TAPE)	MAT'L NO (ON STRIP)	ENG NO (ON STRIP)	WIRE GAGE	COLOR	MWID	"L" MAX	"T" MAX	"H" REF
192770002	AA-5261-LIF	192770003	AA-5261T-LIF	192770001	AA-5261Z-LIF	22-18	RED	.116 (2.95)	.88 (22.4)	.21 (5.3)	1.43 (36.3)
192770005	BB-5263-LIF	192770006	BB-5263T-LIF	192770004	BB-5263Z-LIF	16-14	BLUE	.139 (3.53)	.89 (22.6)		
192770008	C-5293-LIF	192770009	C-5293T-LIF	192770007	C-5293Z-LIF	12-10	YELLOW	.231 (5.87)	1.02 (25.9)	.24 (6.1)	1.51 (38.4)





PARTS ON TAPE





NOTES:
1. MATERIAL: TERMINAL - TIN PLATED BRASS.
   FERRULE - TIN PLATED COPPER ALLOY.
   INSULATION - NYLON, SEE CHART FOR COLOR.
2. MWID = MAXIMUM WIRE INSULATION DIAMETER.
3. MUST BE RoHS COMPLIANT.

DOCUMENT STATUS	P1	RELEASE DATE	2025/09/16 16:37:16

FORMAT: Eng-lega-master-tb-prod-C
REVISION: E1
DATE: 2021/05/01

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

FUNCTIONAL SYMBOLS
FA = 0
FC = 0
FP = 0
DIVISIONAL SYMBOLS

DIMENSION UNITS	SCALE
INCH/MM	NTS

GENERAL TOLERANCES (UNLESS SPECIFIED)

	MM	INCH
4 PLACES	±	±
3 PLACES	±	± 0.005
2 PLACES	± 0.13	± 0.01
1 PLACE	± 0.25	±
0 PLACES	±	±
ANGULAR TOL	± 0.5 °	

DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS

CURRENT REV DESC: REDRAWN TO NX, UPDATED CHART

EC NO: 834716
DRWN: DEANNM1 2025/09/10
CHK'D: ETHRODAHL 2025/09/16
APPR: ETHRODAHL 2025/09/16

INITIAL REVISION:
DRWN:
APPR:

THIRD ANGLE PROJECTION | DRAWING: C-SIZE | SERIES: 19277

molex

QUIXON LOW INSERT FORCE
FULLY INSUL QUICK DISCNT AVIKRIMP 22-10 AWG
FOR .250 X .032 TAB

PRODUCT CUSTOMER DRAWING

DOCUMENT NUMBER	DOC TYPE	DOC PART	REVISION
SD-19277-001	PSD	001	A1

MATERIAL NUMBER	CUSTOMER	SHEET NUMBER
	GENERAL MARKET	1 OF 1