



SIGN	DATE	DESCRIPTION	APPROVER
⚠	10/12'09	Add is cULus MARK	Aaron
		THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!	





SECTION B-B





SECTION A-A

Material:
- Item ① Terminal housing: Thermoplastic (UL94V-0)
- Item ② Clamp : Brass, Ni plated
- Item ③ Wire guard solder pin : Brass,Tin plated
- Item ④ Terminal Screw: "-" slot Steel zinc plated.
- Item ⑤ Terminal cover : Thermoplastic (UL94V-0)

Electrical:	cULus
Voltage rating:	300 V
Current rating:	30 A
Wire range:	
Solid wire(AWG):	10-26
Stranded wire(AWG):	10-26
Torque:	9 Lb-In
Screw:	M3.5
Wire strip length:	7-8 mm
Withstanding Voltage:	1.6KV
Operating temperature:	-40°C to +115°C
⚠ Safety Approval:	cULus

E 4 xx 0 1 x 0 xxxx G

No. OF POLES
02: 2 POLES
:
:
06: 06 POLES

COLOR
0: BLACK
5: GREEN (RAL 6018/T)
6: BLUE
8: GREY (RAL 7004/P)

G: Pb<40000ppm

0000: "@" Logo (Standard)
000A: "ANYTEK" Mark

Any special item by customer requst. please contact sales department.

POLE	2	3	4	6
A	20.00	31.00	38.00	52.00
B	/	11.00	18.00	32.00
Tol.	±0.10	±0.15	±0.20	±0.30

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	E4 Series			DWG NO.	8E40001	
PART NO.	E4xx01x0xxxxG			CUST NO.		Tolerance
APPROVED	CHECKED	DESIGNED	DRAWN	UNIT: mm		X. ±0.50
		Aaron 2009.10.12	Aaron 2009.10.12	SCALE: NONE		X.X ±0.30
				SHEET: 01/01	REV.: C	X.XX ±0.10 X° ±1°