2-292234-2 ✔ ACTIVE

TE Internal #: 2-292234-2

Connector Assembly, Plug, Wire-to-Wire, 22 Position, 1.5 mm [.059 in] Centerline, Crimp/IDC, 2 Row, Black, Wire & Cable, Signal, Panel Mount

View on TE.com >

Connectors > PCB Connectors > Wire-to-Board Connectors > Wire-to-Board Connector Assemblies & Housings > Mini CT Drawer Connector Assemblies



Connector Product Type: **Connector Assembly**

Connector & Housing Type: **Plug**

Connector System: **Wire-to-Wire**

Number of Positions: **22**

Centerline (Pitch): **1.5 mm [.059 in]**

All Mini CT Drawer Connector Assemblies (15)

Features

Packaging Features

Packaging Method	Loose Piece

Product Type Features

Connector Product Type	Connector Assembly
Connector & Housing Type	Plug
Connector System	Wire-to-Wire
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	22
Number of Rows	2

Body Features

Primary Product Color	Black

Contact Features

Contact Current Rating (Max)	1 A

Termination Features

Termination Method to Wire & Cable	Crimp/IDC

Mechanical Attachment

Mating Retention	Without
Connector Mounting Type	Panel Mount

Housing Features

Centerline (Pitch)	1.5 mm[.059 in]

Dimensions

Row-to-Row Spacing	3 mm[.118 in]

Usage Conditions

Operating Temperature Range	-30 – 105 °C[-22 – 221 °F]

Operation/Application

Circuit Application	Signal

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part


numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

Compatible Parts




TE Part # 2-292236-2
1.5 MINI CT DRAWER 22P REC

Customers Also Bought



TE Part #3-1473562-4
RITS CONN. PLUG ASSY 4P ORANGE



TE Part #316455-1
M-U-M-N-L CAP CABLE CLAMP



TE Part #1-172169-9
9 POS TR MINI UNIV



TE Part #5-1473574-4
RITS.JUNCTION BOX 4D 4P F/H



TE Part #3-353293-2
1.5MM CT MT REC ASSY 12P BLACK



TE Part #2-292215-9
MINI CT SGL RELAY 9P BLACK

TE Part #1-2260862-0
F07 APF CABLE ASSY 0.15M

TE Part #2260862-1
F07 APF CABLE ASSY 0.5M

TE Part #8-292112-3
MT REC ASSY (#26,28)

TE Part #1-2260862-1
F07 APF CABLE ASSY 0.3M

Documents

Product Drawings

1.5 MINI CT DRAWER 22P PLUG

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2-292234-2_B.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2-292234-2_B.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2-292234-2_B.3d_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Datasheets & Catalog Pages

Low Power Drawer Connectors QRG

English

Product Specifications

Product Specification

English

AMP COMMON TERMINATION (CT), CONNECTOR, 2mm PITCH, M/T TYPE, LEAD FREE VERSION

Japanese

Product Specification

Japanese