



RoHS compliant
by exemption








PCB hole pattern, mounting side





3	4	Signal contact	S1 / Brass	AuroPur
2	1	Shell	Steel	tin plated
1	1	Insulator	PBT (-55°C to +130°C) acc. UL94V-0	green
No.	*St.*	*Part*	*Type Description/Material*	*Surface plating/Colour/Class*

FUNCTIONAL SYMBOLS
= 0
= 0
= 0

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

DIMENSION UNITS: mm
SCALE: 2:1
MEASUREMENTS WITHOUT TOLERANCE ACC. TO: ISO 2768-m

REV.	CH.-NO.
3	24410
2	24130
1	

CURRENT REVISION
DRWN: DRAWN BY msteinbrueck 20-12-2023
APPR: APPR BY mteubel 11-01-2024

INITIAL REVISION
DRWN: DRAWN BY mteubel 18-10-2018
APPR: APPR BY tschneider01 18-10-2018

molex

FCT D-Sub Mixed-Layout Connector

PRODUCT CUSTOMER DRAWING

REPLACEMENT FOR:	FRIST ANGLE PROJECTION	DRAWING	DOCUMENT NUMBER	CUSTOMER	SHEET NUMBER
1731071282_Rev. A1		A3-SIZE	FM5W1S1A-K121	GENERAL MARKET	1 OF 1

MATERIAL NUMBER: 1731071282
REVISION: 3

COMMENT:
ALL RIGHTS ARE RESERVED BY US FOR THIS DRAWING. WITHOUT OUR PRIOR CONSENT, IT MAY NEITHER BE DUBLICATED NOR MADE AVAILABLE TO A THIRD PARTY, AND IT ALSO MAY NOT BE IMPROPERLY USED BY TE RECEIVER, OR A THIRD PARTY.