



LOOSE PIECE		TAPE MOUNTED		DIMENSIONS				DIMENSIONS						FINISH
MATERIAL NUMBER	ENGINEERING NUMBER	MATERIAL NUMBER	ENGINEERING NUMBER	STUD SIZE	S ±.005	W MAX	C MIN	ID MIN	MWID	B REF	L MAX	H REF	T REF	INSULATION COLOR
191270007	AA-815-06	191270009	AA-815-06T	6	.146/3.71	.301/7.6	.207/5.3	.054/1.37	.138/3.51	.400/10.16	.781/19.84	.08/2.0	.031/0.79	RED
191270010	AA-815-08	191270011	AA-815-08T	8	.173/4.39	.301/7.6	.207/5.3	.054/1.37	.138/3.51	.400/10.16	.781/19.84	.08/2.0	.031/0.79	RED
191270012	AA-815-10	191270013	AA-815-10T	10	.198/5.03	.301/7.6	.207/5.3	.054/1.37	.138/3.51	.400/10.16	.781/19.84	.08/2.0	.031/0.79	RED
191270039	BB-816-06	191270041	BB-816-06T	6	.146/3.71	.301/7.6	.209/5.3	.081/2.06	.165/4.19	.400/10.16	.810/20.32	.08/2.0	.031/0.79	BLUE
191270042	BB-816-08	191270044	BB-816-08T	8	.173/4.39	.301/7.6	.209/5.3	.081/2.06	.165/4.19	.400/10.16	.810/20.32	.08/2.0	.031/0.79	BLUE
191270099	BB-816-10	— — — —	— — — —	10	.198/5.03	.301/7.6	.209/5.3	.081/2.06	.165/4.19	.400/10.16	.810/20.32	.08/2.0	.031/0.79	BLUE
— — — —	— — — —	— — — —	— — — —	— —	— — — —	— — — —	— — — —	— — — —	— — — —	— — — —	— — — —	— — — —	— — — —	— — — —
191270086	C-817-08	191270087	C-817-08T	8	.173/4.39	.385/9.8	.270/6.85	.128/3.25	.225/5.71	.560/14.22	1.046/26.57	.10/2.5	.040/1.02	YELLOW
191270089	C-817-10	191270090	C-817-10T	10	.209/5.3	.385/9.8	.270/6.85	.128/3.25	.225/5.71	.560/14.22	1.046/26.57	.10/2.5	.040/1.02	YELLOW







PARTS ON TAPE









ALLOWABLE BENDING OF AA & BB PARTS.
PARTS WILL FLATTEN OUT DURING INSTALLATION.

C2

NOTES:
1. MATERIAL: COPPER
2. PLATING: ELECTRO-TIN
3. MWID = MAXIMUM WIRE INSULATION DIAMETER
4. PART IS RoHS COMPLIANT

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

DIMENSION UNITS	SCALE
IN/MM	4:1

GENERAL TOLERANCES (UNLESS SPECIFIED)

	MM	INCH
4 PLACES	±	±
3 PLACES	±	± 0.005
2 PLACES	± 0.13	± 0.01
1 PLACE	± 0.25	±
0 PLACES	±	±
ANGULAR TOL	± 0.5 °	

DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS

CURRENT REV DESC: ADD ALLOWABLE BENDING DETAIL VIEW W/ DIM'S..

EC NO: 708739
DRWN: DMYRICK 2022/05/26
CHK'D: JMACNEIL 2022/06/01
APPR: JMACNEIL 2022/06/01

INITIAL REVISION:
DRWN: DLM 2003/08/25
APPR: RWD 2003/08/25

THIRD ANGLE PROJECTION | DRAWING: B-SIZE | SERIES: 19127

molex

FLANGED SPADE TERMINAL, AVIKRIMP -800 SERIES

PRODUCT CUSTOMER DRAWING

DOCUMENT NUMBER	DOC TYPE	DOC PART	REVISION
SD-19127-003	PSD	001	C2

MATERIAL NUMBER	CUSTOMER	SHEET NUMBER
SEE TABLE	GENERAL MARKET	1 OF 1

DOCUMENT STATUS	P1	RELEASE DATE	2022/06/01 22:05:58

FORMAT: Eng-lega-prod-B
REVISION: D
DATE: 2018/01/18