









PCB参考图



NO	Operating Type	Part No.
1	Push To Lock	PB-22E86L
2	Push No Lock	PB-22E86N

NOTE:
1. Operating Force: 300gf±50gf
2. Travel : 2.4±0.2mm

电路简示图



ITEM	PART NAME	QTY.	MATERIAL	FINISHING
⑧	Terminal	6	Brass strip	Plating silver
⑦	Contact	2	Phosphor bronze	Plating silver
⑥	Securing glue	2	POM	Black
⑤	Spring	1	SUS	Natural
④	Base	1	POM	Black
③	Crochet Needle	1	SUS	Natural
②	Cover	1	POM	White
①	KNOB	1	POM	Blue

APPROVALS				DATE			
DRAWN	G.M.Chen	2025/5/14					
CHECKED							
APPROVALS							
TOLERANCES ARE				30 ^{±0.15}	±0.30	ANGLE	PART NO.
				10 ^{±0.10}	±0.20		
				5 ^{±0.10}	±0.15	±2°	UNIT: mm
							SCALE: 1:1
							SHEET 1 OF 1
							PROJ. 1

DEALON 德隆
ELECTRONICS CO.,LTD

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
	A		NEW			