BORN SEMICONDUCTOR


BM2300

N-Channel MOSFET

Features

- V_{DS}=20V
- I_D=3.6A
- $R_{DS(ON)}$ @V_{GS}=4.5V, TYP=30mΩ
- $R_{DS(ON)}$ @V_{GS}=2.5V, TYP=35mΩ


Package



Description

- Super High dense cell design for extremely low $R_{DS(ON)}$
- Reliable and Rugged.
- SOT-23 for Surface Mount Package.

Marking



Ordering information

Order code	Package	Marking	Base qty	Delivery mode
BM2300	SOT-23	A006	3K	Tape and reel

Absolute Maximum Ratings (@T_A=25°C unless otherwise noted)

Symbol	Parameter		Value	Unit
V_{DS}	Drain-Source Voltage		20	V
V_{GS}	Gate-Source Voltage		±12	V
I_D	Continuous Drain Current		3.6	A
I_{DM}	Pulsed Drain Current (1)		8	A
P_D	Maximum Power Dissipation	T_A = 25°C	1.25	W
		T_A = 75°C	0.8	W
T_J,T_{stg}	Operating Junction and Storage Temperature Range		-55 to + 150	°C
$R_{\theta JA}$	Junction-to-Ambient Thermal Resistance (PCB mounted) (2)		78	°C/W

Notes:(1)Pulse width limited by maximum junction temperature.

(2)Surface Mounted on FR4 Board, t < 5 sec.

BORN SEMICONDUCTOR , INC. ALL RIGHT RESERVED

Specifications are subject to change without notice.
Please refer to http://*www.born-tw.com* for current information.

Revision: 2022-Jan-1-A

BM2300

N-Channel MOSFET

Electrical Characteristics @T_A=25°C unless otherwise noted

Symbol	Parameter	Test Condition	Min.	Typ.	Max.	Unit
Static(3)						
BV_{DS}	Drain-Source Breakdown Voltage	V_{GS} = 0V, I_D = 250uA	20	–	–	V
$R_{DS(on)}$	Drain-Source On-State Resistance	V_{GS} = 2.5V, I_D = 3.1A	–	35.0	60.0	mΩ
$R_{DS(on)}$	Drain-Source On-State Resistance	V_{GS} = 4.5V, I_D = 3.6A	–	30.0	55.0	
$V_{GS(th)}$	Gate Threshold Voltage	V_{DS} = V_{GS}, I_D = 250uA	0.4	0.65	1.5	V
I_{DSS}	Zero Gate Voltage Drain Current	V_{DS} = 20V, V_{GS} = 0V	–	–	1	uA
I_{GSS}	Gate Body Leakage	V_{GS} = ±12V, V_{DS} = 0V	–	–	±100	nA
g_{fs}	Forward Transconductance	V_{DS} = 5V, I_D = 4.2A	–	5	–	S
Dynamic(4)						
Q_g	Total Gate Charge	V_{DS} = 10V	–	5.4	–	nC
Q_{gs}	Gate-Source Charge	I_D = 3.6A,	–	0.65	–	
Q_{gd}	Gate-Drain Charge	V_{GS} = 4.5V	–	1.5	–	
$t_{d(on)}$	Turn-On Delay Time	V_{DD} = 10V, R_G = 6Ω,	–	12	–	ns
t_r	Turn-On Rise Time	I_D = 1A,	–	36	–	
$t_{d(off)}$	Turn-Off Delay Time	V_{GS} = 4.5V,	–	34	–	
t_f	Turn-Off Fall Time	R_L = 5.5Ω	–	10	–	
C_{iss}	Input Capacitance	V_{DS} = 10V,	–	340	–	pF
C_{oss}	Output Capacitance	V_{GS} = 0V,	–	115	–	
C_{rss}	Reverse Transfer Capacitance	f = 1.0MHZ	–	33	–	
Source-Drain Diode						
I_S	Max. Diode Forward Current		–	–	1.6	A
V_{SD}	Diode Forward Voltage	I_S = 1.0A,V_{GS} = 0V,	–	–	1.0	V

Notes:(3)Short duration test pulse used to minimize self-heating effect.

(4)Pulse test pulse width <=300us,duty cycle <= 2%.

BORN SEMICONDUCTOR , INC. ALL RIGHT RESERVED

Specifications are subject to change without notice.
Please refer to http://*www.born-tw.com* for current information.

BM2300

N-Channel MOSFET

Typical Performance Characteristics(T_J = 25 °C, unless otherwise noted)

Figure 1 :Output Characteristics




Figure 2 :Transfer Characteristics




Figure 3 :On-Resistance vs. Drain Current




Figure 4 :Capacitance




Figure 5 :Gate Charge





Figure 6 : On-Resistance vs. Junction Temperature



BORN SEMICONDUCTOR , INC. ALL RIGHT RESERVED


Specifications are subject to change without notice.
Please refer to http://www.born-tw.com for current information.

Revision: 2022-Jan-1-A

BM2300


N-Channel MOSFET

Outline Drawing - SOT-23




SYMBOL	MILLIMETER		
	MIN.	Typ.	MAX.
A	0.90	1.00	1.10
A1	0.01	–	0.10
A2	0.50	0.60	0.70
D	2.80	2.90	3.00
b	0.25	0.35	0.45
E	2.10	2.30	2.50
E1	1.20	1.30	1.40
e	1.80	1.90	2.00
L	0.25	0.35	0.45
θ	0	–	8°

Packaging Tape - SOT-23



SYMBOL	MILLIMETER
A0	2.10±0.10
A1	3.10±0.10
B0	0.65±0.10
B1	2.75±0.10
d0	1.55±0.10
d1	1.00±0.05
E	1.75±0.10
F	3.50±0.10
K0	1.10±0.10
P	4.00±0.10
P0	4.00±0.10
P1	2.00±0.10
W	8.00±0.30
T	0.20 ±0.05

Packaging Reel



SYMBOL	MILLIMETER
A	177.8±0.2
B	3.1
C	13.50
D	9.6±0.3
E	75±0.2
F	12.3±0.3
T1	1.0±0.2
Quantity	3000PCS

BORN SEMICONDUCTOR , INC. ALL RIGHT RESERVED